



<b>Rating</b>
16A 125V AC 10A 250V AC
<b>Contact resistance</b>
50mΩ Max
<b>Insulation resistance</b>
DC 500V 100MΩ Min
<b>Dielectric strength</b>
AC 1500V 1 minute
<b>Cut-out</b>

	X	Y
	X	Y
0.75-1.25	26.7-0.1	25.8+0.1
1.25-2	26.9-0.1	25.8+0.1
2-3	27.3-0.1	25.8+0.1

## FEATURES

- \* MATERIAL: Frames are nylon (UL flame: 94V-2). Terminals are silver plated brass.
- \* Illuminated actuators are molded in PC, available with red, amber and green colors.
- \* Snap-in mounting, easy to install switch into panel.

## R13- -

ROCKER	FUNCTION		TERMINAL
<b>1 0 4</b>  	<b>A</b>  <b>4P DPST</b>	<b>H</b>  <b>6P DPDT</b>	  
<b>1 0 5</b>  	<b>B</b>  <b>4P DPST (ILLUMINATED)</b> 125V AC 33KΩ / 250V AC 150KΩ	<b>I</b>  <b>6P DPDT</b>	
	<b>C</b>  <b>6P DPDT</b>		
	<b>D</b>  <b>6P DPDT</b>		