







Rating	30A 12V DC	Mounting Hole	Diagram
Contact Resistance	50m ohm Max.		OFF--ON--ON 
Insulation Resistance	DC 500V 100M ohm Min.		
Dielectric Strength	AC 1500V 1 minute		
Switch Function	PUSH/PULL OFF-ON-ON		



								△
								△
Date	Name	Description						NO
Drawn	Checked	Approved	SCI No.	1120204		Model Name	Push/Pull Switch	
黃維東	研發部 陳仕強		Customer No.			Model No.	A3-20B	
6/29/'07	李元生		Unit	mm	SHIN CHIN INDUSTRIAL CO., LTD.			