


ANTI-VANDAL PUSHBUTTONS

PUSH BUTTON SWITCH



- Φ 19mm diameter
- 2A/48VDC
- 1NO
- The Front Shape:Domed
- The crust material:Stainless Steel/
Brass(Nikel Plated,Gold Plated)
- IP Degree:IP65

GQ19 - B




PUSH BUTTON SWITCH



- Φ 19mm diameter
- 2A/48VDC
- 1NO
- The Front Shape:Flat Round
- The crust material:Stainless Steel/
Brass(Nikel Plated,Gold Plated)
- IP Degree:IP65

GQ19 - F




PUSH BUTTON SWITCH



- Φ 19mm diameter
- 2A/48VDC
- 1NO
- The Front Shape:High Round
- The crust material:Stainless Steel/
Brass(Nikel Plated,Gold Plated)
- IP Degree:IP65

GQ19 - H



Specification		GQ19 - B	GQ19 - F	GQ19 - H
The Front Shape		Domed	Flat Round	High Round
Terminal Type		Screw Terminals	Screw Terminals	Screw Terminals
Switching		No.1	No.1	No.1
Max.Switch Rating		2A/48VDC	2A/48VDC	2A/48VDC
Contact Resistance		≤50mΩ	≤50mΩ	≤50mΩ
Insulation Resistance		≥1000MΩ	≥1000MΩ	≥1000MΩ
Dielectric Strength		2000VAC	2000VAC	2000VAC
Operation Temp.		-20℃ ~ +70℃	-20℃ ~ +70℃	-20℃ ~ +70℃
Mechanical Life		1,000,000cycles	1,000,000cycles	1,000,000cycles
Electrical Life		200,000cycles	200,000cycles	200,000cycles
Contact Material		Silver Alloy	Silver Alloy	Silver Alloy
Panel Thickness		1~8mm	1~8mm	1~8mm
Torque		5~14Nm	5~14Nm	5~14Nm
Operation Temp.		5.5N	5.5N	5.5N
IP Degree		IP65	IP65	IP65
Material	Button	Stainless Steel/Brass(Nikel Plated,Gold Plated)	Stainless Steel/Brass(Nikel Plated,Gold Plated)	Stainless Steel/Brass(Nikel Plated,Gold Plated)
	Body	Stainless Steel/Brass(Nikel Plated,Gold Plated)	Stainless Steel/Brass(Nikel Plated,Gold Plated)	Stainless Steel/Brass(Nikel Plated,Gold Plated)
	Base	PBT	PBT	PBT
RoHS		Made to order	Made to order	Made to order