



Rating	21A 14VDC
Contact R.	50m ohm Max.
Insulation R.	DC 500V 100M ohm Min.
Operation Temp.	-20 ~ 85°C
Operation force	
Safety approval	

Mount Hole		
	X	Y
Thickness	X	Y
0.75~5mm 0.03~0.2inch	36.8-0.1 1.45'-0.04'	15.2-0.1 .60'-0.04'



Material: Case and bottom are nylon-66, actuator is nylon-66 with 33% glass fiber, terminals are silver plated copper, lens is PC. Waterproof and dust proof to IP-66. UV resistant.



發行  
91.12.24  
研發部

Donny/projects/R13-258-mpc0010

△	Date	Name	Descriptions			
Drawing	Check	Approval	SCI No.	Model Name	Rocker Switch	
張曉斌		<i>[Signature]</i>	Customer No.	Model No.	R13-258B	
09/18/02		<i>[Signature]</i>	Unit	mm(inch)	● Shin Chin Industrial Co., Ltd	