




Rating	20A 125VAC, 3/4HP 10A 250VAC, 3/4HP 20A 14VAC 10A 24VAC		Mounting Hole			Circuit Diagram
	10(4)A 250V~					
Contact Resistance	50m ohm Max.				Thickness	X
Insulation Resietance	DC 500V 100M ohm Min.		0.75~5mm 0.03~0.2inch	36.8 ^{+0.2} _{-0.2} 1.45 ^{+0.008} _{-0.008}	15.3 ^{+0.2} _{-0.2} .60 ^{+0.008} _{-0.008}	
Operation Temperature	-20°C~85°C					
Operation force	800±200 gram					
Material: Case and bottom are nylon-66, actuator is						

Material: Case and bottom are nylon-66, actuator is nylon-66 with 33% glass fiber, terminals are silver plated copper.
Waterproof and dust proof to IP-56.
UV resistant.



CEI

						△	
Date	Name	Descriptions				NO	
Drawn	Checked	Approved	SCI No.	1822933	Model Name	Rocker Switch	
黄平平	杨建12		Customer No.		Model No.	R13-258I	REV.
07/10/'08	07/10/08		Unit	mm(inch)	SHIN CHIN INDUSTRIAL CO., LTD.		0