



Rating	50A 12VDC Max.(Start Switch) 20A 12VDC (Toggle Switch) 20mA 12VDC (LED Indicator)	Mounting Hole	Circuit Diagram
Contact Resistance	50m ohm Max.		
Insulation Resistance	DC 500V 100M ohm Min.		
Dielectric Strength	AC 1500V 1 minute		
Operation Temperature	-25°C~85°C		

Descriptions:





Switch: R13-423L3 3P SPST ON-OFF (RED LED).



Indicator: R9-100L (RED LED).

Push switch: A2-23B-07, 3P SPST (ON)-OFF (RED LED).

Safety Cover: R17-10, RED.

Panel: Aluminum, Water Transfer Printed, Carbon.



					△ NO	
Date	Name	Description				
Drawn	Checked	Approved	SCI BOM No.	1130302	Model Name	Panel Switch
C.J.Chan			Customer No.		Model No.	R18-Q1A-23B423L3R17100L
06/15/'09			Unit	mm	SHIN CHIN INDUSTRIAL CO., LTD. 0	