


Rating	15A Max. 12VDC	Mounting Hole	Circuit Diagram
Contact Resistance	50M ohm Max.		
Insulation Resistance	DC 500V 100M ohm Min.		
Dielectric Strength	AC 1000V 1 minute		
Operation Temperature	-20°C~85°C		
Switch Function	4P ON - OFF - ON - momentarily ON turn left - Key IN - right - right EIN - AUS - EIN - Taster	Thickness: 5.5mm max.	



Schlüssel lässt sich  
nur in OFF-Position  
abziehen.

#### MATERIAL:

Frame: PBT (94V-0), Black  
Bottom: PBT (94V-0), Black  
Terminals: Copper Alloy  
Contacts: Copper Alloy+AgSn02In03

Date	Name	Description				NO
Drawn	Checked	Approved	SCI BOM No.	1840111	Model Name	KEY SWITCH
C.J.Chan			Customer No.		Model No.	K3-33C1-07
2/2/'10			Unit	mm		SHIN CHIN INDUSTRIAL CO., LTD. 0