



Canon PGI-29 MBK/PBK/DGY/GY/LGY/CO 6 Ink Cartridge Multipack

Brand : Canon

Product code: 4868B018

Product name : PGI-29 MBK/PBK/DGY/GY/LGY/CO 6 Ink Cartridge Multipack



- Genuine Canon Ink produces on average 35% more quality prints than imitation cartridges***
 - Genuine Canon Ink provides consistent quality prints 100% of the time***
 - Genuine Canon Ink is 100% reliable so you can print with less stress***
 - Return every ink and toner cartridge to be reused or recycled. It's free, easy and environmentally friendly.
- PGI-29 MBK/PBK/DGY/GY/LGY/CO 6 Ink Cartridge Multipack

Canon PGI-29 MBK/PBK/DGY/GY/LGY/CO 6 Ink Cartridge Multipack:

This multipack contains one each of matte black, photo black, dark grey, grey and light grey ink tanks. The set of five colour 36ml ink tanks offer you convenience and savings. The LUCIA system delivers stunning results and longevity. Print up to print up to 1345 photos in 10x15cm or 505 in A3+ size in black and up to up to 1755 photos in 10x15cm or 281 in A3+ size in colour at ISO/JIS-SCID* standard. Canon PGI-29 MBK/PBK/DGY/GY/LGY/CO 6 Ink Cartridge Multipack. Supply type: Multi pack, Colour ink volume: 36 ml, Printing colours: Black, Dark Grey, Grey, Light grey, Matte black, Photo black

Features		Features	
Compatibility *	PIXMA PRO-1	Printing colours *	Black, Dark Grey, Grey, Light grey, Matte black, Photo black
Colour ink cartridges quantity	6	Brand compatibility *	Canon
Colour ink volume	36 ml	Supply type *	Multi pack
Type *	Original	Country of origin	Japan
Ink type	Dye-based ink / Pigment-based ink	Logistics data	
		Harmonized System (HS) code	84439990



8714574623214

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.