Epson Wireless LAN Adapter - ELPAP10



Brand : Epson

Product code: V12H731P01

Product name : Wireless LAN Adapter - ELPAP10

Wireless LAN Adapter - ELPAP10

Epson Wireless LAN Adapter - ELPAP10:

When used with Epson EasyMP Network Monitor and Network Projection software, users can remotely access and control projectors and display content over a wireless network.

• Compliant with IEEE 802.11 b/g/n standards
• Uses USB type A connector
• Compatible with PC or Mac
• Able to transmit audio
• Replacement to ELPAP07
Epson Wireless LAN Adapter - ELPAP10. Product type: USB Wi-Fi adapter, Brand compatibility: Epson, Product colour: White. Connectivity technology: Wired, Host interface: USB, USB connector type: USB Type-A. Package width: 37 mm, Package depth: 182 mm, Package height: 114 mm. Products per pallet: 1200 pc(s), Quantity per pack: 1 pc(s), Pallet gross length: 120 cm

Features	
Product type *	USB Wi-Fi adapter
Brand compatibility *	Epson
Product colour	White
Compatibility	EB-1970W, EB-1975W, EB-1985WU, EB-520, EB-525W, EB-530, EB-535W, EB-536Wi, EB-S04, EB-S31, EB-U04, EB-W04, EB-W31, EB-X31, Epson EB-1761W, Epson EB-1771W, Epson EB-1776W, Epson EB-1945W, Epson EB-1965
Ports & interfaces	
Connectivity technology	Wired
Host interface	USB
USB connector type	USB Type-A
Wi-Fi standards	802.11b, 802.11g, Wi-Fi 4 (802.11n)
Weight & dimensions	
Package width	37 mm
Package depth	182 mm
Package height	114 mm

Weight & dimensions	
Package weight	0.13 g
Technical details	
Country of origin	Philippines
Logistics data	
Products per pallet	1200 pc(s)
Quantity per pack	1 pc(s)
Pallet gross length	120 cm
Pallet gross width	80 cm
Pallet gross height	23 cm
Products per pallet layer	120 pc(s)
Products per pallet layer (UK)	150 pc(s)
Products per pallet (UK)	1500 pc(s)
Pallet length (UK)	120 cm
Pallet width (UK)	100 cm
Pallet height (UK)	23 cm
Harmonized System (HS) code	85299097

8715946552668

Catalog Object Cloud

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 28-APR-2026. Prints or copies of Information are only valid on the printed Publication date