

Epson ELPDC13 document camera White 25.4 / 2.7 mm (1 / 2.7") CMOS

Brand : Epson

Product code: V12H757040DA

Product name : ELPDC13

1/2.7", CMOS, 1920 x 1080, 30fps, A3, digital zoom 16, auto focus, freeze

Epson ELPDC13. Optical sensor size: 25.4 / 2.7 mm (1 / 2.7"), Sensor type: CMOS, Supported graphics resolutions: 1024 x 768 (XGA), 1280 x 1024 (SXGA), 1280 x 800 (WXGA), 1360 x 768 (WXGA), 1920 x 1080 (HD 1080). Digital zoom: 16x, Shooting area (WxD): 297 x 420 mm. USB connector type: USB Type-B. Power consumption (typical): 13 W. Width: 270 mm, Depth: 317 mm, Height: 447 mm



Camera		System requirements	
Optical sensor size *	25.4 / 2.7 mm (1 / 2.7")	Windows operating systems supported	✓
Sensor type *	CMOS	Mac operating systems supported	✓
Supported graphics resolutions *	1024 x 768 (XGA), 1280 x 1024 (SXGA), 1280 x 800 (WXGA), 1360 x 768 (WXGA), 1920 x 1080 (HD 1080)	Weight & dimensions	
Maximum frame rate	30 fps	Width	270 mm
Image freeze *	✓	Depth	317 mm
Light source	LED	Height	447 mm
Lens system		Weight	2.5 kg
Auto focus	✓	Dimensions folded (WxDxH)	367 x 122 x 120 mm
Digital zoom	16x	Packaging data	
Shooting area (WxD)	297 x 420 mm	Quantity per pack	1 pc(s)
Ports & interfaces		Package width	235 mm
USB connector type	USB Type-B	Package depth	445 mm
VGA (D-Sub) input ports	1	Package height	180 mm
VGA (D-Sub) output ports	1	Package weight	4.58 kg
Technical details		Logistics data	
Document size (max)	A3	Products per pallet	66 pc(s)
Product colour *	White	Pallet gross length	120 cm
Cable lock slot	✓	Pallet gross width	80 cm
Cable lock slot type	Kensington	Pallet gross height	5.04 m
Built-in microphone	✓	Products per pallet layer	6 pc(s)
Illumination	✓	Products per pallet layer (UK)	10 pc(s)
Country of origin	Philippines	Products per pallet (UK)	110 pc(s)
Power		Pallet length (UK)	120 cm
Power consumption (typical)	13 W	Pallet width (UK)	100 cm
		Pallet height (UK)	5.04 m



8715946610092

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.