# APC Rack PDU 2G, Metered-by-Outlet, ZeroU, 11.0kW, 230V, (21) C13 & (3) C19



**Brand :** APC

**Product code:** AP8481

**Product name :** Rack PDU 2G, Metered-by-Outlet, ZeroU, 11.0kW, 230V, (21) C13 & (3) C19

Rack PDU 2G, Metered-by-Outlet, ZeroU, 11.0kW, 230V, (21) C13 & (3) C19

APC Rack PDU 2G, Metered-by-Outlet, ZeroU, 11.0kW, 230V, (21) C13 & (3) C19:

APC Metered by Outlet Rack Power Distribution Units (PDUs) provide individual outlet power metering to enable energy optimization and circuit protection Current metering provides real-time remote monitoring of connected loads Metered by Outlet Rack PDUs provide power utilization data to allow Data Center Managers to make informed decisions on load balancing and right sizing IT environments to lower total cost of ownership Metered by Outlet Rack PDUs include real power monitoring, a temperature/humidity sensor port, locking IEC receptacles, and ultra low profile circuit breakers Users can access and configure Metered by Outlet Rack PDUs through secure Web, SNMP, or Telnet Interfaces which are complimented by APC Centralized Management platforms using InfraStruxure Central, Operations, Capacity, and Energy Efficiency

| Design | |
|---|---|
| PDU types * | Metered, Metered-by-outlet |
| Rack capacity * | 0U |
| Mounting | Vertical |
| Product colour | Black |
| **Ports & interfaces** | |
| AC outlets quantity * | 24 AC outlet(s) |
| Power plug | IEC309 |
| AC outlet types * | C13 coupler, C19 coupler |
| Input connection type | IEC 309 16A 3P+N+PE, IEC 309 20A 3P+N+E |
| Output connections | 21 x C13 & 3 x C19 |
| **Features** | |
| LED indicators | ✔ |
| Cable length | 1.83 m |
| **Management features** | |
| Monitoring | Current, Power, Voltage |
| Management platform | Web, SNMP, Telnet |
| **Power** | |
| Nominal input voltage * | 400 V |
| AC input frequency | 50 - 60 Hz |
| Nominal output voltage | 230 V |
| Load capacity | 11040 VA |
| Maximum input current per phase | 16 A |
| Maximum total current draw per phase | 16 A |
| Maximum power | 11040 W |

| Certificates | |
|---|---|
| Compliance certificates | RoHS |
| Certification | EN 55022 Class A, EN 55024, EN 61000-3-2, EN 61000-3-3, FCC Part 15 Class A, ICES-003, UL, VDE, REACH |
| **Operational conditions** | |
| Operating temperature (T-T) | -5 - 45 °C |
| Storage temperature (T-T) | -25 - 65 °C |
| Operating relative humidity (H-H) | 5 - 95% |
| Storage relative humidity (H-H) | 5 - 95% |
| Operating altitude | 0 - 15000 m |
| **Weight & dimensions** | |
| Width | 56 mm |
| Depth | 51 mm |
| Height | 1829 mm |
| Weight | 8.21 kg |
| **Packaging data** | |
| Package weight | 10.5 kg |
| Package width | 163 mm |
| Package depth | 117 mm |
| Package height | 2037 mm |
| **Logistics data** | |
| Total carbon footprint (kg of CO2e) | 7251.82 |



0731304317609



731304317609

**Catalog Object Cloud**



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 28-APR-2026. Prints or copies of Information are only valid on the printed Publication date