

Epson Photo Paper Glossy - A3 - 20 sheets

Brand : Epson

Product code: C13S042536

Product name : Photo Paper Glossy - A3 - 20 sheets

Photo Paper Glossy - A3 - 20 sheets

Epson Photo Paper Glossy - A3 - 20 sheets. Finish type: Gloss, Media weight: 200 g/m², Paper size: A3. Quantity per pack: 1 pc(s), Package width: 310 mm, Package depth: 435 mm. Pallet width (UK): 100 cm, Pallet length (UK): 120 cm, Pallet height (UK): 36 cm. Country of origin: Japan



Features		Packaging data	
Paper size	A3	Package depth	435 mm
Finish type *	Gloss	Package height	15 mm
Media weight *	200 g/m²	Package weight	890 g
Sheets per pack	20 sheets	Logistics data	
Compatible products	Stylus Photo 1200, Stylus Color 1160, Stylus Photo 1270, Epson Stylus Pro 7000, Epson Stylus Pro 10000, Epson Stylus Photo 1290, Stylus Photo 1290 Silver, Epson Stylus Pro 4000 - 17, Stylus Photo R1800, Stylus Photo R2400, Epson Stylus Pro 3800 - 17" A2, Stylus Photo 1410, Stylus Photo R1900, Epson Stylus Pro 4880 - 17" A2, Stylus Photo R2880, Stylus Office T1100, Stylus Photo R3000, WorkForce WF-7510, Stylus Photo R2000, Epson Artisan 1430, WorkForce WF-7520, WorkForce 7010, WorkForce WF-7620, WorkForce WF-7610, Expression Photo XP-950, SureColor P600, Expression Photo XP-960, SureColor P405, Epson SureColor T3160 - 24", Epson SureColor T5160 - 36", Expression Premium XP-900, Epson SureColor T3460 - 24", Epson SureColor T5460 - 36", Expression Premium ET-7750, WorkForce WF-7710, WorkForce WF-7720, WorkForce WF-7725, Expression Photo HD XP-15000, Expression Photo XP-970, SureColor T5460M - 36", Epson Stylus Pro 9000, Epson Stylus Pro 10600 DYE	Harmonized System (HS) code	37032000
		Pallet width (UK)	100 cm
		Pallet length (UK)	120 cm
		Pallet height (UK)	36 cm
		Pallet gross width	80 cm
		Pallet gross length	120 cm
		Pallet gross height	36 cm
		Products per pallet	56 pc(s)
		Products per pallet (UK)	84 pc(s)
		Products per pallet layer	4 pc(s)
		Products per pallet layer (UK)	6 pc(s)
		Master (outer) case width	342 mm
		Master (outer) case length	451 mm
		Master (outer) case height	146 mm
		Products per master (outer) case	10 pc(s)
Packaging data		Other features	
Quantity per pack	1 pc(s)	Country of origin	Japan
Package width	310 mm		



8715946529219



0010343907782



010343907782

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.