

Brother BT5000Y ink cartridge Original Extra (Super) High Yield Yellow

Brand : Brother

Product code: BT5000Y

Product name : BT5000Y

Ultra High Yellow Ink Yield Approx. 5,000 pages

Brother BT5000Y ink cartridge Original Extra (Super) High Yield Yellow:

Colour Inkjet Multi-Function Centres

Brother Colour Inkjet MFCs are the perfect technology for your home and office. The range allows you to colour scan, copy, print and fax from one compact unit designed for your use. Eliminating the frustration of having to throw away unused inks, Brother's colour inkjet machines have separate ink cartridges for each colour. All you have to do is replace the empty cartridge - reducing waste and cost.

Quoted yields are extrapolated based on brother original methodology using Test Patterns ISO/IEC 24712

Benefits of Using Genuine Brother Ink Cartridges?

Specially Formulated Ink for Smooth Printing

Brother ink is specially formulated to achieve the right fluidity to flow through critical points of the print head with ease. This ensures a balanced distribution of ink on the page, resulting in a more optimal balance of colours.



Features		Weight & dimensions	
Colour ink type	Pigment-based ink	Depth	120 mm
Print technology	Inkjet printing	Height	60 mm
Compatibility *	DCPT300, DCPT500W, DCPT700W, MFCT800W, DCPT510W, DCPT710W, MFCT810W, MFCT910DW	Weight	66 g
		Packaging data	
Colour ink cartridges quantity	1	Package weight	107 g
Colour ink page yield *	5000 pages	Package type	Box
Type *	Original	Logistics data	
Cartridge capacity	Extra (Super) High Yield	Pallet gross height	12.8 cm
Ink type	Pigment-based ink	Products per pallet	1920 pc(s)
Printing colours *	Yellow	Master (outer) cases per pallet	96 pc(s)
Brand compatibility *	Brother	Layers per pallet	8 pc(s)
OEM code	BT5000Y	Master (outer) cases per pallet layer	12 pc(s)
Country of origin	Philippines	Pallet gross weight	221.3 kg
Weight & dimensions		Harmonized System (HS) code	84439990
Width	47 mm	Pallet type	800 x 1200 mm



4977766748780

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.