



Canon PFI-1000M Magenta Ink Cartridge

Brand : Canon

Product code: 0548C001

Product name : PFI-1000M Magenta Ink Cartridge

- Genuine Canon Ink produces on average 35% more quality prints than imitation cartridges²
 - Genuine Canon Ink provides consistent quality prints 100% of the time²
 - Genuine Canon Ink is 100% reliable so you can print with less stress²
 - Return every ink and toner cartridge to be reused or recycled. It's free, easy and environmentally friendly.
- PFI-1000M Magenta Ink Cartridge



Canon PFI-1000M Magenta Ink Cartridge:

Bring your images to life with the LUCIA PRO ink range of professional inks for detailed and reliable results. This pigment-based ink system delivers a variety of deep, rich colours and sets your prints apart with outstanding photo permanence. The 80ml magenta ink tank allows you to print up to 5885 photos in 10x15cm or 965 in A2 size at ISO/IEC 29103¹ standard.

Canon PFI-1000M Magenta Ink Cartridge. Colour ink type: Pigment-based ink, Colour ink page yield: 5885 pages, Colour ink volume: 80 ml, Printing colours: Magenta

Features		Features	
Colour ink type	Pigment-based ink	Printing colours *	Magenta
Compatibility *	Canon imagePROGRAF PRO-1000	Brand compatibility *	Canon
Colour ink volume	80 ml	Country of origin	Japan
Colour ink page yield *	5885 pages	Other features	
Type *	Original	Volume	80 ml
Ink type	Pigment-based ink	Logistics data	
		Harmonized System (HS) code	84439990



4549292046403



5715063155943

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.