

StarTech.com 4-Port PCI Express USB 3.0 Card

Brand : StarTech.com

Product code: PEXUSB3S42

Product name : 4-Port PCI Express USB 3.0 Card

StarTech.com 4 Port PCI Express USB 3.0 Card - 3 External and 1 Internal - Native OS Support in Windows 8 and 7 - Standard and Low-Profile
StarTech.com 4-Port PCI Express USB 3.0 Card. Host interface: PCIe, Output interface: USB 3.2 Gen 1 (3.1 Gen 1), Expansion card form factor: Full-height / Low-profile. Product colour: Black, Stainless steel, Maximum cable length: 3 m, Certification: CE, FCC. Chipset: 2 x Renesas / NEC - µPD720202, Data transfer rate (max): 5 Gbit/s. Windows operating systems supported: Windows 10 Education, Windows 10 Education x64, Windows 10 Enterprise, Windows 10 Enterprise x64,...., Server operating systems supported: Windows Server 2008 R2, Windows Server 2012. Width: 15 mm, Depth: 167 mm, Height: 120 mm



Ports & interfaces		System requirements	
Host interface *	PCIe		Windows 10 Education, Windows 10 Education x64, Windows 10 Enterprise, Windows 10 Enterprise x64, Windows 10 Home, Windows 10 Home x64, Windows 10 Pro, Windows 10 Pro x64, Windows 7 Enterprise, Windows 7 Enterprise x64, Windows 7 Home Basic, Windows 7 Home Basic x64, Windows 7 Home Premium, Windows 7 Home Premium x64, Windows 7 Professional, Windows 7 Professional x64, Windows 7 Starter, Windows 7 Starter x64, Windows 7 Ultimate, Windows 7 Ultimate x64, Windows 8, Windows 8 Enterprise, Windows 8 Enterprise x64, Windows 8 Pro, Windows 8 Pro x64, Windows 8.1, Windows 8.1 Enterprise, Windows 8.1 Enterprise x64, Windows 8.1 Pro, Windows 8.1 Pro x64, Windows 8.1 x64, Windows Vista Business, Windows Vista Business x64, Windows Vista Enterprise, Windows Vista Enterprise x64, Windows Vista Home Basic, Windows Vista Home Basic x64, Windows Vista Home Premium, Windows Vista Home Premium x64, Windows Vista Ultimate, Windows Vista Ultimate x64, Windows XP Home, Windows XP Home x64, Windows XP Professional, Windows XP Professional x64
Output interface *	USB 3.2 Gen 1 (3.1 Gen 1)		
Expansion card form factor	Full-height / Low-profile		
Expansion card standard	PCI 2.0		
USB 3.2 Gen 1 (3.1 Gen 1) Type-A ports quantity	4		
Design		Windows operating systems supported	
Internal *	✓		
Product colour	Black, Stainless steel		
Maximum cable length	3 m		
Hot-swap	✓		
Certification	CE, FCC		
Features		Linux operating systems supported ✓	Windows Server 2008 R2, Windows Server 2012
Chipset	2 x Renesas / NEC - µPD720202		
Data transfer rate (max)	5 Gbit/s		
UASP support	✓		
Operational conditions			
Operating temperature (T-T)	5 - 50 °C		
Storage temperature (T-T)	-20 - 60 °C		
Operating relative humidity (H-H)	20 - 80%		

Technical details	
Compliance certificates	RoHS
Weight & dimensions	
Width	15 mm
Depth	167 mm
Height	120 mm
Weight	90 g
Packaging data	
Mounting brackets included	✓
Drivers included	✓
Manual	✓
Package width	171 mm
Package depth	144 mm
Package height	30 mm
Package weight	141 g
Logistics data	
Harmonized System (HS) code	84733020



0065030860321



065030860321



0758399140967



758399140967

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.