

StarTech.com USB to 5.5mm Power Cable - Type N Barrel - 1m

Brand : StarTech.com

Product code: USB2TYPEN1M

Product name : USB to 5.5mm Power Cable - Type N Barrel - 1m

StarTech.com 1m USB to Type N Barrel 5V DC Power Cable - USB A to 5.5mm DC - 1 Meter USB to 5.5mm DC Plug

StarTech.com USB to 5.5mm Power Cable - Type N Barrel - 1m:

Tired of having to carry around a separate wall adapter in order to power or charge your 5V devices, such as certain external hard drives, streaming media players, and Bluetooth® speakers?

This 1m USB power cable makes it easier to power 5V DC devices that have a Type N (OD: 5.5mm, ID:2.5mm) barrel power connector. You can power or charge the devices through an available USB port on your laptop or desktop computer.

Expertly designed and constructed of high-quality materials, the StarTech.com USB2TYPEN1M power cable is backed by our lifetime warranty.

The StarTech.com Advantage

- Guaranteed reliability
StarTech.com USB to 5.5mm Power Cable - Type N Barrel - 1m. Cable length: 1 m, Connector 1: USB A, Connector 2: Barrel type N



Features		Weight & dimensions	
Product colour *	Black	Width	15 mm
Connector 1 gender *	Male	Depth	1000 mm
Connector 2 gender *	Male	Height	8 mm
Cable length *	1 m	Diameter	5.5 mm
Connector 1 *	USB A	Weight	27 g
Connector 2 *	Barrel type N	Packaging data	
Connector 1 form factor	Straight	Quantity per pack	1 pc(s)
Connector 2 form factor	Straight	Package width	144 mm
Connector contacts plating	Nickel	Package depth	118 mm
Connector angle	90°	Package height	10 mm
AWG wire size	28	Package weight	34 g
Cable shielding	Aluminum mylar foil	Logistics data	
Certificates		Harmonized System (HS) code	84733080
Compliance certificates	RoHS		



0065030848664



065030848664



0650308486640



650308486640



0012302581934



012302581934

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.