

StarTech.com 2 Port USB HDMI KVM Switch with Audio and USB 2.0 Hub

Brand : StarTech.com

Product code: SV231HDMIUA

Product name : 2 Port USB HDMI KVM Switch with Audio and USB 2.0 Hub

StarTech.com 2 Port USB HDMI KVM Switch with Audio and USB 2.0 Hub

StarTech.com 2 Port USB HDMI KVM Switch with Audio and USB 2.0 Hub. Keyboard port type: USB, Mouse port type: USB, Video port type: HDMI. HD type: Full HD, Maximum resolution: 1920 x 1200 pixels. Product colour: Black, Mean time between failures (MTBF): 126813 h, Certification: ROHS. Input voltage: 100 - 240, 12 V, Input current: 0.8 A, Output current: 1.5 A. Width: 125 mm, Depth: 70 mm, Height: 40 mm



Ports & interfaces

Number of computers controlled *	2
Keyboard port type *	USB
Mouse port type *	USB
Video port type *	HDMI
Console ports *	3.5mm headphone, 3.5mm mic, HDMI, USB A
Console USB ports quantity	4
Headphone outputs	3
Number of microphone inputs	3

Performance

HD type *	Full HD
Maximum resolution *	1920 x 1200 pixels
Daisy chain	✗

Design

Rack mounting *	✗
Product colour *	Black
Mean time between failures (MTBF)	126813 h
Certification	ROHS

Display

On Screen Display (OSD)	✗
-------------------------	---

Power

Input voltage	100 - 240, 12 V
Input current	0.8 A
Output current	1.5 A
Power consumption (typical)	18 W
Power plug type	Type M

Operational conditions

Operating temperature (T-T)	0 - 40 °C
Storage temperature (T-T)	-20 - 60 °C
Operating relative humidity (H-H)	0 - 80%

Weight & dimensions

Width	125 mm
Depth	70 mm
Height	40 mm
Weight	634 g

Packaging data

Package width	188 mm
Package depth	250 mm
Package height	100 mm
Package weight	1.1 kg

Packaging content

Manual	✓
AC adapter included	✓
Rubber feet	✓

Other features

Connectivity technology	Wired
I/O ports	1x HDMI (F) 4x USB A (F) 6x 3.5mm (F) 2x USB B (F) 2x mini-HDMI (F)
Dimensions (WxDxH)	124.8 x 70 x 40 mm
Ports quantity	2
Power requirements	AC 110 - 240 V

Logistics data

Harmonized System (HS) code	85176200
-----------------------------	----------



0065030837521



065030837521



0132017927497



132017927497

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.