

StarTech.com 4 Port Dual DVI USB KVM Switch with Audio & USB 2.0 Hub

Brand : StarTech.com

Product code: SV431DD2DUA

Product name : 4 Port Dual DVI USB KVM Switch with Audio & USB 2.0 Hub



4 Port Dual DVI USB KVM Switch with Audio & USB 2.0 Hub

StarTech.com 4 Port Dual DVI USB KVM Switch with Audio & USB 2.0 Hub. Keyboard port type: USB, Mouse port type: USB, Video port type: DVI-I. Maximum resolution: 2048 x 1536 pixels, Maximum digital resolution: 1920 x 1200 pixels, Maximum analog resolution: 2048 x 1536 pixels. Product colour: Black, Housing material: Steel, LED indicators: Power. Input voltage: 100-240 V, Input current: 0.8 A, Output voltage: 12 V. Compliance certificates: RoHS



Ports & interfaces

Number of computers controlled *	4
Keyboard port type *	USB
Mouse port type *	USB
Video port type *	DVI-I
Console ports *	3.5mm headphone, 3.5mm mic, DVI-I, USB A
USB 2.0 ports quantity	4
USB connector type	USB Type-A
Audio connections	✓
Number of microphone inputs	1
DC-in jack	✓

Network

Ethernet LAN	✗
--------------	---

Performance

Maximum resolution *	2048 x 1536 pixels
Maximum digital resolution	1920 x 1200 pixels
Maximum analog resolution	2048 x 1536 pixels
Daisy chain	✗
Number of users	1 user(s)

Design

Product colour *	Black
Housing material	Steel
LED indicators	Power
Certification	CE, FCC, UL

Power

Input voltage	100-240 V
Input current	0.8 A

Power

Output voltage	12 V
Output current	1.5 A
Compatible power plug types	AU, EU, UK, US

Sustainability

Compliance certificates	RoHS
-------------------------	------

Operational conditions

Operating temperature (T-T)	0 - 40 °C
Storage temperature (T-T)	-20 - 60 °C
Operating relative humidity (H-H)	0 - 90%

Weight & dimensions

Width	220 mm
Depth	130 mm
Height	60 mm
Weight	1.25 kg

Packaging data

Package width	295 mm
Package depth	245 mm
Package height	86 mm
Package weight	1.88 kg

Packaging content

Manual	✓
AC adapter included	✓
Rubber feet	✓

Other features

IP control	✗
------------	---

Logistics data

Harmonized System (HS) code	85176200
-----------------------------	----------



0065030835695



065030835695



0666669825035



666669825035

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.