StarTech.com 30m Coax High Resolution Monitor VGA Video Cable - HD15 M/M



Brand : StarTech.com

Product code: MXTMMHQ30M

Product name : 30m Coax High Resolution Monitor VGA Video Cable - HD15 M/M

30m Coax High Resolution Monitor VGA Video Cable - HD15 M/M



StarTech.com 30m Coax High Resolution Monitor VGA Video Cable - HD15 M/M:

Connect your VGA monitor with the highest quality connection available
The MXTMMHQ30M High Resolution VGA Cable (30-meter) is designed to provide the highest video quality possible through VGA, ideally suited for high resolution applications of 1920x1200 and above. This durably constructed coaxial VGA video cable (HD15 to HD15) eliminates the picture "ghosting" and fuzzy images that are inherent to non-coaxial VGA cables, while delivering superior EMI interference protection by using ferrite cores near the connector ends.
The StarTech.com Advantage
- Supports high resolution VGA video (1920x1200 or above), suitable for a wide range of applications
- Ferrite cores to help eliminate EMI interference
- Backed by StarTech.com Lifetime warranty

Features	
Cable length *	30 m
Connector 1 *	VGA (D-Sub)
Connector 2 *	VGA (D-Sub)
Connector 1 gender *	Male
Connector 2 gender *	Male
Product colour *	Black
Connector contacts plating	Nickel
Operational conditions	
Operating temperature (T-T)	0 - 60 °C
Storage temperature (T-T)	-20 - 80 °C

Operational conditions	
Operating relative humidity (H-H)	0 - 80%
Weight & dimensions	
Weight	2.9 kg
Packaging data	
Package width	350 mm
Package depth	460 mm
Package height	81 mm
Package weight	2.76 kg
Logistics data	
Harmonized System (HS) code	84733080

0065030847605

065030847605

Catalog Object Cloud

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 28-APR-2026. Prints or copies of Information are only valid on the printed Publication date