StarTech.com 1 Port Metal Industrial USB to RS422/RS485 Serial Adapter w/ Isolation



Brand : StarTech.com

Product code: ICUSB422IS

Product name : 1 Port Metal Industrial USB to RS422/RS485 Serial Adapter w/ Isolation

1 Port Metal Industrial USB to RS422/RS485 Serial Adapter w/ Isolation
StarTech.com 1 Port Metal Industrial USB to RS422/RS485 Serial Adapter w/ Isolation. Connector 1: USB B, Connector 2: RS-422/485, Cable length: 1.8 m. Product colour: Black



Ports & interfaces	
Connector 1 *	USB B
Connector 2 *	RS-422/485
Connector 1 gender	Male
Connector 2 gender	Female
Cable length	1.8 m

Performance	
Product colour *	Black
Data transfer rate	0.00088 Gbit/s
Compatible operating systems	Windows CE (4.2, 5.0, 6.0), XP Embedded, 98SE, 2000, XP, Vista, 7, 8, 8.1, 10, 11 Windows Server 2003, 2008 R2, 2012, 2012 R2, 2016, 2019 macOS 10.6 to 10.15, 11.0, 12.0, 13.0 Linux Kernel 3.0.x+

Power	
Input voltage	5 V


Operational conditions	
Operating temperature (T-T)	0 - 55 °C
Storage temperature (T-T)	-20 - 85 °C
Relative humidity	5 - 95%

Weight & dimensions	
Width	64 mm
Depth	118 mm
Height	23 mm
Weight	180 g

Packaging content	
Quantity per pack	1 pc(s)
Cables included	USB

Packaging data	
Package width	45 mm
Package depth	230 mm
Package height	160 mm
Package weight	390 g

Logistics data	
Products per master (outer) case	50 pc(s)
Master (outer) case width	502 mm
Master (outer) case length	400 mm
Master (outer) case height	511 mm



0065030830683



065030830683



0710931110821



710931110821

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 28-APR-2026. Prints or copies of Information are only valid on the printed Publication date