



APC Smart-UPS On-Line, 6kVA/6kW, Rackmount 4U, 230V, 6x C13+4x C19 IEC outlets, Network Card+SmartSlot, Extended runtime, W/ rail kit, Marine



Brand : APC

Product code: SRT6KRMXLIM

Product name : Smart-UPS On-Line, 6kVA/6kW, Rackmount 4U, 230V, 6x C13+4x C19 IEC outlets, Network Card+SmartSlot, Extended runtime, W/ rail kit, Marine

Smart-UPS On-Line, 6kVA/6kW, Rackmount 4U, 230V, 6x C13+4x C19 IEC outlets, Network Card+SmartSlot, Extended runtime, W/ rail kit, Marine
APC Smart-UPS On-Line, 6kVA/6kW, Rackmount 4U, 230V, 6x C13+4x C19 IEC outlets, Network Card+SmartSlot, Extended runtime, W/ rail kit, Marine. UPS topology: Double-conversion (Online), Output power capacity: 6 kVA, Output power: 6000 W. AC outlet types: C13 coupler, C19 coupler, IEC Jumpers, Power plug: Terminal, AC outlets quantity: 13 AC outlet(s). Battery technology: Sealed Lead Acid (VRLA), Battery life (max): 5 year(s), Battery recharge time: 1 h. Form factor: Rackmount, Product colour: Black, Rack capacity: 4U. Compliance certificates: RoHS, Certification: CE, EAC, RCM, VDE, REACH

Features		Battery	
UPS topology *	Double-conversion (Online)	Battery life (max)	5 year(s)
Output power capacity *	6 kVA	Battery recharge time	1 h
Output power *	6000 W	Hot-swap battery	✓
Waveform *	Sine	Automatic battery test	✓
Input operation voltage (min) *	160 V	Design	
Input operation voltage (max) *	275 V	Form factor *	Rackmount
Input frequency *	40 - 70 Hz	Rack capacity	4U
Output operation voltage (min)	220 V	Product colour *	Black
Output operation voltage (max)	240 V	Display type	LCD
Output frequency	50/60 Hz	LED indicators	✓
Surge energy rating	480 J	International Protection (IP) code	IP20
Crest factor	3:1	Operational conditions	
Emergency Power Off (EPO)	✓	Operating temperature (T-T)	0 - 40 °C
Output voltage Total Harmonic Distortion (THD)	3%	Storage temperature (T-T)	-15 - 45 °C
Noise level	55 dB	Operating relative humidity (H-H)	0 - 95%
Surge protection	✓	Storage relative humidity (H-H)	0 - 95%
Audible alarm(s)	✓	Operating altitude	0 - 3000 m
Auto-restart	✓	Non-operating altitude	0 - 15000 m
Temperature voltage compensation	✓	Certificates	
Ports & interfaces		Compliance certificates	RoHS
AC outlet types	C13 coupler, C19 coupler, IEC Jumpers	Certification	CE, EAC, RCM, VDE, REACH
Power plug	Terminal	Weight & dimensions	
AC outlets quantity	13 AC outlet(s)	Width	432 mm
USB port	✓	Depth	719 mm
USB 2.0 ports quantity	1	Height	174 mm
Serial interface	✓	Weight	60 kg
Ethernet LAN (RJ-45) ports	1	Packaging data	
Cabling technology	10/100Base-T	Package width	610 mm
SmartSlot	✓	Package depth	960 mm
Battery		Package height	370 mm
Battery technology	Sealed Lead Acid (VRLA)	Package volume	67000 cm ³
Number of batteries supported	1	Logistics data	
		Products per pallet	6 pc(s)
		Harmonized System (HS) code	85078000
		Total carbon footprint (kg of CO2e)	55428.62



0731304320838



731304320838

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.