

Epson Kiwi Singlepack Magenta 202 Claria Premium Ink

Brand : EpsonProduct family: KiwiProduct code: C13T02F34020

Product name : Singlepack
Magenta 202 Claria Premium Ink

Singlepack Magenta 202 Claria Premium Ink
Epson Kiwi Singlepack Magenta 202 Claria Premium Ink. Colour ink type: Pigment-based ink, Cartridge capacity: Standard Yield, Colour ink page yield: 300 pages, Colour ink volume: 4.1 ml, Printing colours: Magenta, Quantity per pack: 1 pc(s)



Features		Logistics data	
Colour ink type	Pigment-based ink	Pallet gross width	80 cm
Print technology	Inkjet printing	Pallet gross length	120 cm
Quantity per pack *	1 pc(s)	Pallet gross height	2 m
Colour ink cartridges quantity	1	Products per pallet	2720 pc(s)
Colour ink volume	4.1 ml	Pallet gross weight	0 g
Colour ink page yield *	300 pages	Master (outer) case width	102 mm
Type *	Original	Master (outer) case length	260 mm
Cartridge capacity	Standard Yield	Master (outer) case height	146 mm
Ink type	Pigment-based ink	Products per master (outer) case	8 pc(s)
Printing colours *	Magenta	Master (outer) case gross weight	0 g
Brand compatibility *	Epson	Master (outer) case GTIN (EAN/UPC)	8715946649139
OEM code	C13T02F34020	Harmonized System (HS) code	84439990
Country of origin	Indonesia	Pallet width (UK)	100 cm
Operational conditions		Pallet length (UK)	120 cm
Storage temperature (T-T)	-20 - 40 °C	Pallet height (UK)	2 m
Packaging data		Pallet weight (UK)	0 g
Package width	100 mm	Products per pallet (UK)	2720 pc(s)
Package depth	142 mm	Products per pallet layer	272 pc(s)
Package height	30 mm	Products per pallet layer (UK)	272 pc(s)
Package weight	37 g	Minimum order quantity	8 pc(s)
Package type	Blister		
Other features			
Certification	CE		



8715946646251

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.