

Brother LC22UC ink cartridge 1 pc(s) Original High (XL) Yield Cyan

Brand : Brother

Product code: LC22UC

Product name : LC22UC

- Prints 1,200 pages in accordance with ISO/IEC 24711.
 - High quality genuine Brother cartridge.
 - Prevents waste to save you paper, time and money.
- The Brother LC22UC Cyan Ink Cartridge – Single Pack. Prints 1,200 pages.

Brother LC22UC ink cartridge 1 pc(s) Original High (XL) Yield Cyan:

This genuine Brother LC22UC Cyan Ink Cartridge has been specially developed to ensure quality documents every time you print. With colour fade resistant properties, you can enjoy sharp, crisp colours that last. By buying our cartridges, you protect your printer from potential long-term damage caused by using non-genuine products.

Brother LC22UC. Cartridge capacity: High (XL) Yield, Supply type: Single pack, Colour ink page yield: 1200 pages, Printing colours: Cyan, Quantity per pack: 1 pc(s)



Features		Packaging data	
Compatibility *	MFC-J985DW, DCP-J785DW	Package weight	72 g
Quantity per pack *	1 pc(s)	Package type	Box
Colour ink cartridges quantity	1	Other features	
Colour ink page yield *	1200 pages	Certification	ISO/IEC 24711
Type *	Original	Logistics data	
Cartridge capacity	High (XL) Yield	Pallet gross height	15 cm
Printing colours *	Cyan	Products per pallet	3000 pc(s)
Brand compatibility *	Brother	Master (outer) cases per pallet	30 pc(s)
Supply type *	Single pack	Layers per pallet	5 pc(s)
Country of origin	Philippines	Master (outer) cases per pallet layer	6 pc(s)
Weight & dimensions		Pallet gross weight	237 kg
Width	23 mm	Harmonized System (HS) code	84439990
Depth	92 mm	Pallet type	800 x 1200 mm
Height	120 mm		
Weight	38 g		



4977766759670



5715328103191

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.