APC NetShelter Cable Management, Vertical Cable Manager, Cable Fall (radius drop), for for NetShelter Racks, and Cable Ladders, Set of 2

Brand : APC

Product code: AR8654

Product name : APC NetShelter Cable Management, Vertical Cable Manager, Cable Fall (radius drop), for for NetShelter Racks, and Cable Ladders, Set of 2

APC NetShelter Cable Management, Vertical Cable Manager, Cable Fall (radius drop), for for NetShelter Racks, and Cable Ladders, Set of 2

APC NetShelter Cable Management, Vertical Cable Manager, Cable Fall (radius drop), for for NetShelter Racks, and Cable Ladders, Set of 2:

Cable Fall AR8654 (radius drop) provides a proper bend radius for cabling routed into/out of enclosures or overhead cable management systems. Cable fall attaches in multiple locations including the enclosure roof holes, open frame rack sides, vertical cable manager openings and rungs of overhead cable ladder systems. Secure cabling in place using slots in the accessory and hook-and-loop fasteners straps (AR8621 not provided).
APC NetShelter Cable Management, Vertical Cable Manager, Cable Fall (radius drop), for for NetShelter Racks, and Cable Ladders, Set of 2. Type: Cable waterfall base, Product colour: Black. Weight: 320 g

Features	
Type *	Cable waterfall base
Product colour *	Black
Built-in fan	✕
Hot-swap	✕
On/off switch	✕
Castor wheels	✕
Locking	✕
Certification	TAA, REACH
Weight & dimensions	
Width	127 mm
Depth (max)	6.4 cm

Weight & dimensions	
Height	64 mm
Weight	320 g
Packaging data	
Package width	112 mm
Package depth	185 mm
Package height	89 mm
Package weight	360 g
Technical details	
Compliance certificates	RoHS
Logistics data	
Harmonized System (HS) code	85389099



7313043011104



0731304301110



731304301110

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 28-APR-2026. Prints or copies of Information are only valid on the printed Publication date