Brother TN-326BK toner cartridge 1 pc(s) Original Black

Brand : Brother

Product code: TN-326BK

Product name : TN-326BK



- Prints 4,000 pages in accordance with ISO/IEC19798
- High quality genuine Brother cartridge
- Prevents waste to save you paper, time and money

The Brother TN326BK Black Toner Cartridge. Prints 4,000 pages.

Brother TN-326BK toner cartridge 1 pc(s) Original Black:

Choose this genuine TN326BK Toner Cartridge to ensure your printer continues to deliver printouts you can be proud of. As it’s a high yield cartridge, the TN326BK in Black lasts longer than a standard cartridge but offers the same excellent quality results.
Brother TN-326BK. Black toner page yield: 4000 pages, Printing colours: Black, Quantity per pack: 1 pc(s)



Features	
Compatibility *	HL-L8250CDN, HL-L8350CDW
Quantity per pack *	1 pc(s)
Black toner page yield *	4000 pages
Type *	Original
Printing colours *	Black
Brand compatibility *	Brother
Product colour	Black
Country of origin	China
Weight & dimensions	
Width	166 mm
Depth	120 mm
Height	340 mm
Weight	558 g
Packaging data	
Package weight	880 g

Packaging data	
Package type	Box
Other features	
Print technology	Laser printing
Page yield footnote	ISO/IEC 19798
Logistics data	
Harmonized System (HS) code	84439990
Master (outer) cases per pallet layer	6 pc(s)
Master (outer) cases per pallet	36 pc(s)
Layers per pallet	6 pc(s)
Products per pallet	144 pc(s)
Pallet gross height	17.4 cm
Pallet gross weight	136.9 kg
Pallet type	800 x 1200 mm

4977766735018

5712505546161

4977766732369

Catalog Object Cloud

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 28-APR-2026. Prints or copies of Information are only valid on the printed Publication date