



Lenovo EN4091 network switch module 10 Gigabit Ethernet, Gigabit Ethernet



Brand : Lenovo
Product code: 88Y6043
Product name : EN4091

Flex System EN4091 10Gb Ethernet Pass-thru Module
Lenovo EN4091. Ethernet interface type: 10 Gigabit Ethernet, Gigabit Ethernet, Ethernet LAN data rates: 1000,10000 Mbit/s, Copper ethernet cabling technology: 1000BASE-T. Fiber optic connector: LC, Fiber ethernet cabling technology: 1000BASE-LX, 1000BASE-SX, 10GBASE-LR, 10GBASE-SR. Dimensions (WxDxH): 401 x 317 x 30 mm, Weight: 3.7 kg

Network		Optical fiber	
Ethernet interface type	10 Gigabit Ethernet, Gigabit Ethernet	Fiber ethernet cabling technology	1000BASE-LX, 1000BASE-SX, 10GBASE-LR, 10GBASE-SR
Ethernet LAN data rates	1000,10000 Mbit/s	Ports & interfaces	
Copper ethernet cabling technology	1000BASE-T	SFP+ module slots quantity	14
Full duplex	✓	Weight & dimensions	
Networking standards	IEEE 802.3ab, IEEE 802.3ae, IEEE 802.3z	Dimensions (WxDxH)	401 x 317 x 30 mm
Optical fiber		Weight	3.7 kg
Fiber optic connector	LC	Logistics data	
		Harmonized System (HS) code	85176990
		Other features	
		SFP/SFP+ slots quantity	14



0883436121873



883436121873



8834361218734

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.