



HP LaserJet Enterprise MFP M725dn

Brand : HP

Product family: LaserJet
Enterprise

Product code: CF066A#B19

Product name : LaserJet
Enterprise MFP M725dn

- 100-sheet ADF; Front-facing USB printing; Scan to email/PDF; Two-sided printing
 - Print, copy, scan
 - Up to 40 ppm (black)
 - Up to 1200 x 1200 dpi
- LaserJet Enterprise MFP M725dn

[HP LaserJet Enterprise MFP M725dn:](#)

Print high-quality documents on an array of paper sizes up to A3, launch one-touch workflows, and manage jobs on the desktop with touchscreen ease. Enable large-volume printing on a wide range of paper sizes – up to A3 – with a 4,600-sheet maximum input capacity.^[1] Preview and edit scanning jobs; centrally manage printing policies; safeguard sensitive business information.

HP LaserJet Enterprise MFP M725dn. Print technology: Laser, Printing: Mono printing, Maximum resolution: 1200 x 1200 DPI. Copying: Mono copying, Maximum copy resolution: 600 x 600 DPI. Scanning: Colour scanning, Optical scanning resolution: 600 x 600 DPI. Duplex functions: Print. Maximum ISO A-series paper size: A3. Direct printing. Product colour: Black, Grey



Printing		Design	
Duplex printing mode	Auto	Control type	Buttons, Touch
Print resolution black	1200 x 1200 DPI	Colour display	✓
Print technology *	Laser	Power	
Printing *	Mono printing	Power consumption (average operating)	890 W
Duplex printing *	✓	Power consumption (PowerSave)	39 W
Maximum resolution *	1200 x 1200 DPI	Power consumption (printing)	890 W
Print speed (black, normal quality, A4/US Letter) *	41 ppm	Power consumption (copying)	890 W
Print speed (black, normal quality, A3)	20 ppm	Power consumption (ready)	39 W
Duplex print speed (ISO/IEC 24734) mono	28 ipm	Power consumption (standby)	6.5 W
Time to first page (black, normal)	10 s	Power consumption (sleep)	6.5 W
Print margins (top, bottom, right, left)	2 mm	Power consumption (off)	0.3 W
Economical printing	✓	Energy Star Typical Electricity Consumption (TEC)	2.8 kWh/week
Secure printing	✓	AC input voltage	220 - 240 V
Copying		AC input frequency	50/60 Hz
Duplex copying *	✓	Brand-specific features	
Copying *	Mono copying	HP Auto-On/Auto-Off	✓
Maximum copy resolution *	600 x 600 DPI	HP Security tools Management security: SNMPv3, SSL/TLS, WPA2-Enterprise, 802.1X authentication (EAP- PEAP, EAP-TLS), IPP over TLS, IPsec/Firewall with Certificate, Pre-Shared Key Authentication, and Kerberos Authentication; Support for WJA-10 IPsec Configuration using IPsec Plug-in	
Copy speed (black, normal quality, A4)	41 cpm		
Maximum number of copies	9999 copies		
Copier resize	25 - 400%		
Auto fit function	✓		

Scanning		Brand-specific features	
Duplex scanning *	✓	HP GTIN (EAN/UPC) with options	(ABT) 887111016812; (ABY) 887111016829; (ACQ) 887111016836; (B13) 888182819586; (B19) 887111016843; (BAZ) 887111016850
Scanning *	Colour scanning		
Optical scanning resolution *	600 x 600 DPI	HP GTIN (EAN/UPC)	887111016812, 887111016829, 887111016836, 888182819586, 887111016843, 887111016850
Maximum scan area	297 x 420 mm		
Scanner type *	Flatbed scanner		
Scan technology	CCD		
Scan to	E-mail, Network folder, USB		
Scan speed (colour)	30 ppm		
Scan speed (black)	50 ppm		
Image formats supported	JPEG, MTIFF, TIFF		
Document formats supported	PDF, XPS		
Input colour depth	24 bit		
Greyscale levels	256		
Fax			
Faxing *	✗		
Features			
Recommended duty cycle	5000 - 20000 pages per month	Server operating systems supported	Windows Server 2003, Windows Server 2008 R2, Windows Server 2008 R2 x64, Windows Server 2008 x64, Windows Server 2008, Windows Server 2012 x64, Windows Server 2012
Maximum duty cycle *	200000 pages per month		
Duplex functions *	Print	Other operating systems supported	Novell, Linux
Digital sender	✓		
Number of print cartridges *	1		
Printing colours *	Black		
Page description languages	PostScript 3, PDF 1.4, PCL 5, PCL 6		
Printer fonts	Scalable, TrueType, Windows, PCL, PostScript		
Number of printer fonts	105		
All-In-One-multitasking	✓		
Optional functions	Fax		
Country of origin	China, Mexico		
Replacement cartridges	HP 14A Black LJ Toner Cartridge CF214A (~10,000 pages); HP 14X Black LJ Toner Cartridge CF214X (~17,500 pages)		
HP segment	Business		
Input & output capacity			
Total number of input trays *	3		
Total input capacity *	600 sheets		
Total output capacity *	250 sheets		
Paper tray 1 input capacity	100 sheets		
Paper tray 2 input capacity	250 sheets		
Multi-Purpose tray	✓		
Multi-Purpose tray input capacity	100 sheets		
Paper input type	Paper tray, Sheetfed		
Auto document feeder (ADF)	✓		
Auto document feeder (ADF) input capacity	100 sheets		
Maximum number of input trays	6		
Maximum input capacity	4600 sheets		
Maximum output capacity	250 sheets		
Paper handling			
Maximum ISO A-series paper size *	A3		
Maximum print size	308 x 465.9 mm		
Paper tray media types *	Plain paper, Bond paper, Recycled paper, Envelopes, Card stock, Labels, Transparencies, Lightweight paper, Rough paper, Letterhead		
ISO A-series sizes (A0...A9) *	A3, A4, A5		
ISO B-series sizes (B0...B9)	B4, B5, B6		
JIS B-series sizes (B0...B9)	B4, B5		
Custom media width	76.2 - 312 mm		
		System requirements	
		Windows operating systems supported	Windows Vista x64, Windows Vista, Windows 7 x64, Windows 7, Windows 8 x64, Windows 8, Windows 10 x64, Windows 10
		Mac operating systems supported	Mac OS X 10.6 Snow Leopard, Mac OS X 10.7.5 Lion, Mac OS X 10.8 Mountain Lion, MacOS
		Linux operating systems supported	✓
		Server operating systems supported	Windows Server 2003, Windows Server 2008 R2, Windows Server 2008 R2 x64, Windows Server 2008 x64, Windows Server 2008, Windows Server 2012 x64, Windows Server 2012
		Other operating systems supported	Novell, Linux
		Operational conditions	
		Operating relative humidity (H-H)	20 - 80%
		Recommended humidity operating range	30 - 70%
		Recommended operating temperature range (T-T)	10 - 32.5 °C
		Storage temperature (T-T)	0 - 60 °C
		Operating temperature (T-T)	10 - 32.5 °C
		Certificates	
		Certification	CISPR 22:2008 / EN 55022:2010 (Class A); EN 61000-3-2 :2006 +A1:2009 +A2:2009; EN 61000-3-3 :2008; EN 55024:1998+A1+A2; EMC Directive 2004/108/EC with CE Marking (Europe); other EMC approvals as required by individual countries
		Sustainability	
		Sustainability compliance	✓
		Sustainability certificates	ENERGY STAR, EPEAT Silver
		Sustainable technologies and materials	Mercury Free
		Doesn't contain	Mercury
		Carbon footprint	
		Total carbon footprint (kg of CO2e)	800
		Carbon emissions, manufacturing (kg of CO2e)	439
		Carbon emissions, logistics (kg of CO2e)	22
		Total carbon emissions, w/o use phase (kg of CO2e)	328
		Weight & dimensions	
		Width	614 mm
		Depth	649 mm
		Height	609 mm
		Weight	54.1 kg
		Packaging data	
		Package width	760 mm
		Package depth	745 mm

Paper handling		Packaging data		
Custom media length	127 - 469.9 mm	Package height	832 mm	
Paper tray media weight	60 - 199 g/m²	Package weight	68.6 kg	
Envelope feeder	No	Packaging content		
Ports & interfaces		Cables included	AC	
Standard interfaces	Ethernet, USB 2.0	Warranty card	✓	
Direct printing *	✓	Quick installation guide	✓	
USB port	✓	Bundled software	Windows Installer, HP PCL 6 discrete driver, Mac Software Link to Web (Postscript emulation driver & Installer on Web), Note: No Mac Software inbox	
USB 2.0 ports quantity	3			
Optional connectivity	Wireless LAN	Logistics data		
Network		Harmonized System (HS) code	84433100	
Wi-Fi *	✗	Pallet gross weight	68.6 kg	
Ethernet LAN *	✓	Technical details		
Cabling technology	10/100/1000Base-T(X)	Box contents	HP Laserjet Enterprise MFP M725dn; HP Black Laserjet Toner Cartridge (~10,000 pages); Printer documentation and software on CD-ROM; Installation guide, Support flyer, Warranty card; Power cord; 2x250-sheet trays.	
Ethernet LAN data rates	10,100,1000 Mbit/s	Compliance certificates	CECP	
Security algorithms	SNMPv3, SSL/TLS, WPA2-Enterprise, EAP-PEAP, EAP-TLS	General Product Safety Regulation (GPSR) URL	https://support.hp.com/gb-en/product/setup-user-guides/hp-laserjet-enterprise-mfp-m725-series/model/5197861?sku=CF066A ; https://h10032.www1.hp.com/ctg/Manual/c03381951.pdf	
Supported network protocols (IPv4)	AutoIP, SLP, Telnet, IGMPv2, BOOTP/DHCP, WINS, IP Direct Mode, WS Print	Other features		
Supported network protocols (IPv6)	DHCPv6, MLDv1, ICMPv6	Number of users	30 user(s)	
Security features	AES 256-bit	Custom media sizes	Tray 1: 76.2 x 127 to 312 x 469.9 mm; Tray 2: 148 x 210 to 297 x 363 mm; Tray 3: 148 x 210 to 297 x 431 mm	
Mobile printing technologies	Mopria Print Service, HP ePrint, Apple AirPrint	Pallet dimensions (W x D x H)	760 x 745 x 832 mm	
Performance		Printer management	HP Web Jetadmin, HP Utility (Mac)	
Maximum internal memory	1536 MB	Recommended system requirements	Windows 10; Windows 8; Windows 7; Windows Vista; Windows Server 2012 (64-bit); Windows Server 2008; Windows Server 2008 R2; Windows Server 2003 (SP1+); 200 MB available hard disk space. Mac OS X 10.6; OS X Lion; OS X Mountain Lion; 1 GB available hard disk space; operating system compatible hardware system requirements; CD-ROM/DVD-ROM or Internet.	
Memory slots	1		Windows 10, Windows 8, Windows 7, Windows Vista, Windows Server 2012 (64-bit), Windows Server 2008 (32-bit/64-bit), Windows Server 2008 R2 (64-bit), Windows Server 2003 (SP1+); Mac OS X v10.6, OS X Lion, OS X Mountain Lion; For the latest operating system support see: Citrix and Windows Terminal Services (http://www.hp.com/go/upd), Novell (http://www.novell.com/iprint), Linux (http://www.hplip.net), UNIX (http://www.hp.com/go/unix , http://www.hp.com/go/unixmodelscripts , http://www.hp.com/go/jetdirectunix_software), SAP device types (http://www.hp.com/go/sap/drivers , http://www.hp.com/go/sap/print), HP ePrint Mobile Driver (http://www.hp.com/go/eprintmobiledriver)	
Internal storage capacity	500 GB		Compatible operating systems	
Internal memory *	1024 MB			
Built-in processor	✓		Acoustic power emissions (ready)	50 dB
Processor frequency	800 MHz	Acoustic pressure emissions bystander (ready)	36 dB	
Sound pressure level (printing)	54 dB	Typical electricity consumption (TEC) number	Blue Angel: 2.8 kWh/Week; Energy Star 3.0: 0.653 kWh/Week	
Sound pressure level (scanning)	52 dB	UNSPSC-code	43212110	
Sound power level (printing)	6.8 dB	All-in-one functions	Copy, Print, Scan	
Design		Colour all-in-one functions	✗	
Product colour *	Black, Grey	Electromagnetic compatibility	CISPR 22:2008 / EN 55022:2010 (Class A); EN 61000-3-2 :2006 +A1:2009 +A2:2009; EN 61000-3-3 :2008; EN 55024:1998+A1+A2; EMC Directive 2004/108/EC with CE Marking (Europe); other EMC approvals as required by individual countries	
Market positioning *	Business			
Built-in display *	✓			
Display	LCD			
Display diagonal	20.3 cm (8")			



0887111016843



887111016843

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 28-APR-2026. Prints or copies of Information are only valid on the printed Publication date