

Epson Value Glossy Photo Paper - 10x15cm - 20 sheets

Brand : Epson

Product code: C13S400037

Product name : Value Glossy Photo Paper - 10x15cm - 20 sheets

- Value for money: Epson quality at an affordable price
- Works hand-in-hand: Our papers are designed to bring out the best in our inks
- Epson quality to everyday life: Even scrapbook photos can look great
- Fit for purpose: A low cost photo paper designed for everyday printing
- Options to suit: A choice of sizes and pack volumes

Value Glossy Photo Paper - 10x15cm - 20 sheets

Epson Value Glossy Photo Paper - 10x15cm - 20 sheets. Finish type: Gloss, Media weight: 183 g/m², Paper size: 10x15 cm. Width: 100 mm, Height: 150 mm, Roll width: 10 cm. Quantity per pack: 1 pc(s), Package width: 112 mm, Package depth: 192 mm. Pallet width (UK): 100 cm, Pallet length (UK): 120 cm, Pallet height (UK): 93.9 cm. Star rating: 3*, Country of origin: Japan



Features		Packaging data	
Paper size	10x15 cm	Quantity per pack	1 pc(s)
Finish type *	Gloss	Package width	112 mm
Media weight *	183 g/m²	Package depth	192 mm
Best uses	Office printing, Calendar, Photo collage, Photo gifts, Photo, Cards and gift wraps, Seasonal decorations and gifts, Masks and party, Daily use	Package height	8 mm
		Package weight	71 g
Sheets per pack	20 sheets	Technical details	
		Master (outer) case GTIN (EAN/UPC) 8715946612249	
		Logistics data	
		Harmonized System (HS) code	37032000
		Pallet width (UK)	100 cm
		Pallet length (UK)	120 cm
		Pallet height (UK)	93.9 cm
		Pallet weight (UK)	0 g
		Pallet gross width	80 cm
		Pallet gross length	120 cm
		Pallet gross height	93.9 cm
		Pallet gross weight	0 g
		Products per pallet	8000 pc(s)
		Products per pallet (UK)	12000 pc(s)
		Products per pallet layer	1000 pc(s)
		Products per pallet layer (UK)	1500 pc(s)
		Master (outer) case width	240 mm
		Master (outer) case length	332 mm
		Master (outer) case height	173 mm
		Master (outer) case gross weight	0 g
		Products per master (outer) case	100 pc(s)
		Other features	
		Star rating	3*
		Country of origin	Japan

Features

Compatible products

- Expression Premium XP-900 -
- Expression Premium XP-830 -
- Expression Premium XP-820 -
- Expression Premium XP-720 -
- Expression Premium XP-710 -
- Expression Premium XP-635 -
- Expression Photo XP-960 -
- Expression Photo XP-950 -
- Expression Photo XP-860 -
- Expression Photo XP-850 -
- Expression Photo XP-760 -
- Expression Photo XP-750 -
- Expression Photo HD XP-15000 -
- Expression Home XP-455 -
- Expression Home XP-452 -
- Expression Home XP-445 -
- Expression Home XP-442 -
- Expression Home XP-435 -
- Expression Home XP-432 -
- Expression Home XP-425 -
- Expression Home XP-422 -
- Expression Home XP-415 -
- Expression Home XP-412 -
- Expression Home XP-355 -
- Expression Home XP-352 -
- Expression Home XP-345 -
- Expression Home XP-342 -
- Expression Home XP-335 -
- Expression Home XP-332 -
- Expression Home XP-325 -
- Expression Home XP-322 -
- Expression Home XP-315 -
- Expression Home XP-312 -
- Expression Home XP-257 -
- Expression Home XP-255 -
- Expression Home XP-247 -
- Expression Home XP-245 -
- Expression Home XP-235 -
- Expression Home XP-225 -
- Expression Home XP-215 -
- Expression Home XP-212 - Epson
- Stylus Photo 1500W - Epson Stylus
- Photo 1400 - Epson Expression
- Premium XP-800 - Epson Expression
- Premium XP-700 - Epson Expression
- Premium XP-605 - Epson Expression
- Premium XP-600 - Epson Expression
- Home XP-405 - Epson Expression
- Home XP-305 - Epson Expression
- Home XP-30 - Epson Expression
- Home XP-205 - Epson Expression
- Home XP-202 - Epson Expression
- Home XP-102

Weight & dimensions

Width	100 mm
Height	150 mm
Roll width	10 cm



8715946611853

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.