

ASUS SDRW-08D2S-U Lite optical disc drive DVD±R/RW White

Brand : ASUS

Product code: 90-DQ0436-UA221KZ

Product name : SDRW-08D2S-U Lite

SDRW-08D2S-U Lite, CD/DVD, USB 2.0, 140ms/160ms, Win/Mac, 280g, White

ASUS SDRW-08D2S-U Lite optical disc drive DVD±R/RW White:

Harmony of Technology and Aethetics

- MAC and Windows 8 Compatible
- Disc Encryption double security with password-controlled and hidden-file functionality
- Drag-and-Burn: friendly interface with only three simple steps to burn a disc
- Diamond-cut design realize aesthetics of technology

ASUS SDRW-08D2S-U LITE is an external slim DVD writer capable of 8X speeds. It's stylish and portable design. The lattice-like appearance of the drive is inspired by diamonds, making the product unique from every angle. Additional features include USB 2.0 and the E-Green Engine for the best optical storage available.

Disc Encryption II

Double security with password-controlled and hidden-file functionality

Drag-and-Burn

Friendly Interface with only three simple steps to burn a disc

Diamond-cut Design

Diamond-Shaped Design realize aesthetics of technology

Design		Reading speed	
Internal *	×	DVD+RW read speed	8x
Product colour	White	Access time	
Disc loading type	Tray	DVD drive average random access time	160 ms
Mounting	Horizontal	CD-ROM drive average random access time	140 ms
Performance		Record modes	
Purpose *	Desktop/Laptop	Track-at-once (TAO)	✓
Optical drive type *	DVD±R/RW	Disc-at-once (DAO)	✓
Interface *	USB 2.0	Session-at-once (SAO)	✓
Disc types supported	CD-R, CD-ROM, CD-RW, DVD+R, DVD+R DL, DVD+RW, DVD-R, DVD-R DL, DVD-RAM, DVD-ROM, DVD-RW	Packet writing	✓
LightScribe	×	Sequential writing	✓
Optical disc diameter	80,120 mm	Random write	✓
Writing speed			
CD write speed *	24x		
CD rewrite speed	16x		
CD-R write speed	24x		
CD-RW write speed	16x		
DVD+R write speed *	8x		
DVD-R write speed	8x		
DVD-R Double Layer write speed	6x		
DVD+R Double Layer write speed	6x		
DVD+RW write speed	8x		
DVD-RW write speed	6x		
DVD-RAM write speed	5x		



Reading speed		System requirements	
CD read speed *	24x	Windows operating systems supported	Windows 7 Home Basic, Windows 7 Home Basic x64, Windows 7 Home Premium, Windows 7 Home Premium x64, Windows 7 Professional, Windows 7 Professional x64, Windows 7 Starter, Windows 7 Starter x64, Windows 7 Ultimate, Windows 7 Ultimate x64, Windows Vista Business, Windows Vista Business x64, Windows Vista Enterprise, Windows Vista Enterprise x64, Windows Vista Home Basic, Windows Vista Home Basic x64, Windows Vista Home Premium, Windows Vista Home Premium x64, Windows Vista Ultimate, Windows Vista Ultimate x64, Windows XP Home, Windows XP Home x64, Windows XP Professional, Windows XP Professional x64
CD-R read speed	24x		
CD-RW read speed	24x		
CD-ROM read speed	24x		
DVD+R read speed	8x		
DVD-R read speed	8x		
DVD-RW read speed	8x		
DVD-RAM read speed	5x		
DVD-ROM read speed	8x		
DVD-R Double Layer read speed	8x		
DVD+R Double Layer read speed	8x	Mac operating systems supported	Mac OS X 10.5 Leopard
Operational conditions			
Operating relative humidity (H-H)		15 - 80%	
Operating temperature (T-T)		5 - 40 °C	
Storage temperature (T-T)		-30 - 60 °C	
Storage relative humidity (H-H)		10 - 90%	
Weight & dimensions			
Width		142 mm	
Depth		142 mm	
Height		20 mm	
Weight		280 g	
Packaging content			
Bundled software		Cyberlink Power2Go 7 E-Green	
Other features			
Power requirements		5V	
Minimum RAM		512 MB	
Minimum processor		Intel Pentium 4 2.0GHz / AMD Athlon 2100+	
Minimum storage drive space		10 GB	
Number of optical discs		1 discs	
Logistics data			
Harmonized System (HS) code		84717030	



4716659385080



5054484679738



5053086063716



5054533679733

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.