



TP-Link AC750 Wi-Fi Range Extender

Brand : TP-Link

Product code: RE200 V2

Product name : AC750 Wi-Fi Range Extender

- Boosts wireless signal to previously unreachable or hard-to-wire areas flawlessly
- Compatible with 802.11 b/g/n and 802.11ac Wi-Fi devices
- Dual band speeds up to 750Mbps
- Miniature size and wall-mounted design make it easy to deploy and move flexibly
- Ethernet port allows the Extender to function as a wireless adapter to connect wired devices
- Works with any Wi-Fi router or wireless access point

IEEE 802.11ac/b/g/n, 2.4 - 5GHz, 10/100Mbps

TP-Link AC750 Wi-Fi Range Extender. Type: Network repeater, Data transfer rate: 750 Mbit/s, Ethernet LAN data rates: 10,100 Mbit/s. Antenna type: Internal. Cabling technology: 10/100Base-T(X), Networking standards: IEEE 802.11ac, IEEE 802.11b, IEEE 802.11g, IEEE 802.11n, Wi-Fi standards: 802.11b, 802.11g, Wi-Fi 4 (802.11n). Product colour: White. Power consumption (typical): 6.5 W



Performance		Design	
Type *	Network repeater	Reset button	✓
Data transfer rate	750 Mbit/s	Power	
Ethernet LAN data rates	10,100 Mbit/s	Power consumption (typical)	6.5 W
Windows operating systems supported	Windows 2000, Windows 2000 Professional, Windows 7 Home Basic, Windows 7 Home Premium, Windows 7 Home Premium x64, Windows 7 Professional, Windows 7 Professional x64, Windows 7 Starter, Windows 7 Starter x64, Windows 7 Ultimate, Windows 7 Ultimate x64, Windows 8, Windows 8 Enterprise, Windows 8 Enterprise x64, Windows 8 Pro, Windows 8 Pro x64, Windows 98SE, Windows NT, Windows Vista Business, Windows Vista Business x64, Windows Vista Enterprise, Windows Vista Enterprise x64, Windows Vista Home Basic, Windows Vista Home Basic x64, Windows Vista Home Premium, Windows Vista Home Premium x64, Windows Vista Ultimate, Windows Vista Ultimate x64, Windows XP Home, Windows XP Home x64, Windows XP Professional, Windows XP Professional x64	Operational conditions	
		Operating temperature (T-T)	0 - 40 °C
		Storage temperature (T-T)	-40 - 70 °C
		Operating relative humidity (H-H)	10 - 90%
		Storage relative humidity (H-H)	5 - 90%
Mac operating systems supported	✓	Weight & dimensions	
		Width	110 mm
		Depth	65.8 mm
Linux operating systems supported	✓	Height	75.2 mm
		Packaging content	
		Cables included	LAN (RJ-45)
Antenna		Quick start guide	✓
		Packaging data	
		Package width	156.5 mm
Antennas quantity	3	Package depth	101.5 mm
Antenna type	Internal	Package height	89 mm
		Package weight	200 g
		Certificates	
		Compliance certificates	RoHS
		Other features	
		Operating temperature (T-T)	32 - 104 °F

Network	
Cabling technology	10/100Base-T(X)
Networking standards	IEEE 802.11ac, IEEE 802.11b, IEEE 802.11g, IEEE 802.11n
Wi-Fi	✓
Wi-Fi standards	802.11b, 802.11g, Wi-Fi 4 (802.11n)
Wi-Fi data rate (max)	433 Mbit/s
Wi-Fi band	Dual-band (2.4 GHz / 5 GHz)
Security algorithms	128-bit WEP, 152-bit WEP, 64-bit WEP, WPA-PSK, WPA2-PSK
Wi-Fi Multimedia (WMM)/(WME)	✓
Ports & interfaces	
Ethernet LAN (RJ-45) ports	1
Design	
Product colour *	White



0845973071875



845973071875



6935364071608



5054242203069

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.