Brother TN-326Y toner cartridge 1 pc(s) Original Yellow

Brand : Brother

Product code: TN-326Y

Product name : TN-326Y



- Prints 3,500 pages in accordance with ISO/IEC19798
- High quality genuine Brother cartridge
- Prevents waste to save you paper, time and money

The Brother TN-326Y Yellow Toner Cartridge. Prints 3,500 pages.

Brother TN-326Y toner cartridge 1 pc(s) Original Yellow:

This replacement TN-326Y high yield toner cartridge in yellow has been specially engineered to work in synergy with your Brother printer. The TN-326Y blends quickly and easily with other colours, delivering documents quickly and in perfect clarity.
Brother TN-326Y. Colour toner page yield: 3500 pages, Printing colours: Yellow, Quantity per pack: 1 pc(s)




Features	
Compatibility *	HL-L8250CDN, HL-L8350CDW
Quantity per pack *	1 pc(s)
Colour toner page yield *	3500 pages
Type *	Original
Printing colours *	Yellow
Brand compatibility *	Brother
Product colour	Black, Yellow
Country of origin	China
Weight & dimensions	
Width	166 mm
Depth	120 mm
Height	340 mm
Weight	563 g
Packaging data	
Package weight	886 g

Packaging data	
Package type	Box
Other features	
Print technology	Laser printing
Page yield footnote	ISO/IEC 19798
Logistics data	
Harmonized System (HS) code	84439990
Master (outer) cases per pallet layer	6 pc(s)
Master (outer) cases per pallet	36 pc(s)
Layers per pallet	6 pc(s)
Products per pallet	144 pc(s)
Pallet gross height	17.3 cm
Pallet gross weight	144.7 kg
Pallet type	800 x 1200 mm



4977766735049



5901535818328



4977766732376

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 28-APR-2026. Prints or copies of Information are only valid on the printed Publication date