



Jabra LINK 14201-41

Brand : Jabra

Product code: 14201-41

Product name : LINK 14201-41

- MPN: 14201-41
 - Original and authentic, manufacturer made accessory.
 - The Jabra LINK™ 14201-41 enables remote Electronic Hook Switch Control (EHS) with Jabra wireless headsets and the Cisco Unified IP deskphone 8941 and 8945.
- LINK 14201-41

Jabra LINK 14201-41:

Control your Cisco phone from your Jabra headset. The Jabra LINK 14201-41 enables remote Electronic Hook Switch Control (EHS) with Jabra wireless headsets and the Cisco Unified IP phone 8941 and 8945. Jabra wireless headsets with EHS functionality boost productivity as they provide the users with the ability to answer and end a call, while away from their desk.

The Jabra LINK™ 14201-41 enables remote Electronic Hook Switch Control (EHS) with Jabra wireless headsets and the Cisco Unified IP deskphone 8941 and 8945.

Jabra LINK 14201-41. Product type: EHS adapter, Product colour: Black



Features		Packaging data	
Product type *	EHS adapter	Package depth	230 mm
Brand compatibility *	Cisco	Package height	20 mm
Compatibility	Jabra PRO 9400, 920, 925 Cisco Unified IP 8941, 8945	Package weight	40 g
Product colour	Black	Logistics data	
Electronic hook switch (EHS)	✓	Harmonized System (HS) code	85189000
Ports & interfaces		Master (outer) case width	167 mm
Bluetooth	✓	Master (outer) case length	595 mm
Packaging content		Master (outer) case height	399 mm
Quantity per pack	1 pc(s)	Master (outer) case gross weight	5.03 kg
Packaging data		Products per master (outer) case	96 pc(s)
Package width	160 mm	Country of origin	China



5706991017465



5054629627082



0706487015451



706487015451

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.