



APC Rack PDU, Switched, 2U, 30A, 208V, (16)C13

Brand : APC

Product code: AP7911B

Product name : Rack PDU, Switched, 2U, 30A, 208V, (16)C13



Rack PDU, Switched, 2U, 30A, 208V, (16)C13
APC Rack PDU, Switched, 2U, 30A, 208V, (16)C13. PDU types: Switched, Rack capacity: 2U, Product colour: Black. AC outlets quantity: 16 AC outlet(s), AC outlet types: C13 coupler, Input connection type: NEMA L6-30P. Cable length: 3.66 m. Monitoring: Current, Outlet control: Recycle, Turn off. Nominal input voltage: 200-230 V, Maximum current: 30 A, AC input frequency: 50 - 60 Hz



Design		Certificates	
PDU types *	Switched	Compliance certificates	RoHS
Rack capacity *	2U	Certification	cUL, CSA, FCC 15 A, ICES-003, PSE, UL 60950, UL
Product colour	Black		
Ports & interfaces		Operational conditions	
AC outlets quantity *	16 AC outlet(s)	Operating temperature (T-T)	0 - 45 °C
AC outlet types *	C13 coupler	Storage temperature (T-T)	-25 - 65 °C
Input connection type	NEMA L6-30P	Operating relative humidity (H-H)	0 - 95%
Features		Storage relative humidity (H-H)	0 - 95%
LED indicators	✓	Operating altitude	0 - 3000 m
Cable length	3.66 m	Non-operating altitude	0 - 15000 m
Management features		Weight & dimensions	
Monitoring	Current	Width	444 mm
Outlet control	Recycle, Turn off	Depth	254 mm
Power		Height	89 mm
Nominal input voltage *	200-230 V	Weight	6.32 kg
AC input frequency	50 - 60 Hz	Packaging data	
Maximum current *	30 A	Package weight	8.36 kg
Maximum input current per phase	30 A	Package width	514 mm
Maximum total current draw per phase	30 A	Package depth	514 mm
		Package height	146 mm



0731304331605



731304331605

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.