

Epson Squirrel Singlepack Light Cyan 378 Claria Photo HD Ink

Brand : Epson

Product family: Squirrel

Product code: C13T37854010

Product name : Singlepack
Light Cyan 378 Claria Photo HD
Ink

Singlepack Light Cyan 378 Claria Photo HD Ink

Epson Squirrel Singlepack Light Cyan 378 Claria Photo HD Ink. Colour ink type: Pigment-based ink, Cartridge capacity: Standard Yield, Colour ink page yield: 360 pages, Colour ink volume: 4.8 ml, Printing colours: Light Cyan, Quantity per pack: 1 pc(s)



Features		Packaging data	
Colour ink type	Pigment-based ink	Package weight	42 g
Print technology	Inkjet printing	Package type	Blister
Compatibility *	- Expression Photo XP-8500 - Expression Photo HD XP-15000	Logistics data	
Quantity per pack *	1 pc(s)	Products per pallet	2720 pc(s)
Colour ink cartridges quantity	1	Pallet gross weight	0 g
Colour ink volume	4.8 ml	Master (outer) case width	102 mm
Colour ink page yield *	360 pages	Master (outer) case length	260 mm
Type *	Original	Master (outer) case height	146 mm
Cartridge capacity	Standard Yield	Products per master (outer) case	8 pc(s)
Ink type	Pigment-based ink	Master (outer) case gross weight	0 g
Printing colours *	Light Cyan	Master (outer) case GTIN (EAN/UPC)	8715946648866
Brand compatibility *	Epson	Harmonized System (HS) code	84439990
OEM code	C13T37854010	Pallet weight (UK)	0 g
Country of origin	Indonesia	Products per pallet (UK)	2720 pc(s)
Packaging data		Products per pallet layer	272 pc(s)
Package width	102 mm	Products per pallet layer (UK)	272 pc(s)
Package depth	33 mm	Minimum order quantity	8 pc(s)
Package height	145 mm		



8715946645803



4058154242957

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.