

Epson Squirrel Singlepack Light Cyan 378XL Claria Photo HD Ink

Brand : Epson Product family: Squirrel Product code: C13T37954020

Product name : Singlepack
Light Cyan 378XL Claria Photo
HD Ink

Singlepack Light Cyan 378XL Claria Photo HD Ink
Epson Squirrel Singlepack Light Cyan 378XL Claria Photo HD Ink. Colour ink type: Pigment-based ink,
Cartridge capacity: High (XL) Yield, Colour ink page yield: 830 pages, Colour ink volume: 10.3 ml,
Printing colours: Light Cyan, Quantity per pack: 1 pc(s)



Features		Logistics data	
Colour ink type	Pigment-based ink	Pallet gross length	120 cm
Print technology	Inkjet printing	Pallet gross height	2 m
Compatibility *	Expression Photo XP-8500, XP-8505	Products per pallet	2720 pc(s)
Quantity per pack *	1 pc(s)	Pallet gross weight	0 g
Colour ink cartridges quantity	1	Master (outer) case width	102 mm
Colour ink volume	10.3 ml	Master (outer) case length	260 mm
Colour ink page yield *	830 pages	Master (outer) case height	146 mm
Type *	Original	Products per master (outer) case	8 pc(s)
Cartridge capacity	High (XL) Yield	Master (outer) case gross weight	0 g
Ink type	Pigment-based ink	Master (outer) case GTIN (EAN/UPC)	8715946648736
Printing colours *	Light Cyan	Harmonized System (HS) code	84439990
Brand compatibility *	Epson	Pallet width (UK)	100 cm
OEM code	C13T37954020	Pallet length (UK)	120 cm
Country of origin	Indonesia	Pallet height (UK)	2 m
Packaging data		Pallet weight (UK)	0 g
Package width	103 mm	Products per pallet (UK)	2720 pc(s)
Package depth	32 mm	Products per pallet layer	272 pc(s)
Package height	146 mm	Products per pallet layer (UK)	272 pc(s)
Package weight	49 g	Minimum order quantity	8 pc(s)
Package type	Blister		
Logistics data			
Pallet gross width	80 cm		



8715946645933

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.