

Epson Photo Paper Glossy - 10x15cm - 500 sheets

Brand : Epson

Product code: C13S042549

Product name : Photo Paper Glossy - 10x15cm - 500 sheets

Photo Paper Glossy - 10x15cm - 500 sheets
Epson Photo Paper Glossy - 10x15cm - 500 sheets. Finish type: Gloss, Media weight: 200 g/m², Sheets per pack: 500 sheets. Width: 100 mm, Height: 150 mm. Quantity per pack: 1 pc(s), Package width: 65 mm, Package depth: 210 mm. Master (outer) case width: 227 mm, Master (outer) case length: 332 mm, Master (outer) case height: 150 mm. Country of origin: Japan



Features		Weight & dimensions	
Finish type *	Gloss	Width	100 mm
Media weight *	200 g/m²	Height	150 mm
Sheets per pack	500 sheets	Packaging data	
Compatible products	- WorkForce WF-7610DWF -	Quantity per pack	1 pc(s)
	WorkForce WF-7110DTW -	Package width	65 mm
	WorkForce WF-3620DWF -	Package depth	210 mm
	WorkForce WF-2750DWF -	Package height	160 mm
	WorkForce WF-2010W - WorkForce	Package weight	1.73 kg
	WF-100W - WorkForce Pro WF-	Logistics data	
	C5790DWF - Expression Premium	Harmonized System (HS) code	37032000
	XP-900 - Expression Premium	Master (outer) case width	227 mm
	XP-630 - Expression Premium	Master (outer) case length	332 mm
	XP-610 - Expression Premium	Master (outer) case height	150 mm
	XP-6000 - Expression Premium	Products per master (outer) case	4 pc(s)
	XP-530 - Expression Photo HD	Minimum order quantity	20 pc(s)
	XP-15000 - Expression Home	Other features	
	XP-425 - Expression Home XP-342 -	Country of origin	Japan
	Expression Home XP-332 -		
	Expression Home XP-245 -		
	Expression Home XP-235 - Epson		
	Stylus Photo 2100 - Epson Stylus		
	Photo 1500W - Epson Stylus Photo		
	1400 - Epson Expression Premium		
	XP-600 - Epson Expression Home		
	XP-405WH - Epson Expression		
	Home XP-405 - Epson Expression		
	Home XP-402 - Epson Expression		
	Home XP-305 - Epson Expression		
	Home XP-302 - Epson Expression		
	Home XP-202 - Epson Expression		
	Home XP-102		



8715946529516

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.