APC AR3340G rack cabinet 42U Freestanding rack Grey



Brand : APC

Product code: AR3340G

Product name : AR3340G

NetShelter SX 42U 750mm Wide x 1200mm Deep Networking Enclosure with Sides Grey RAL7035

APC AR3340G rack cabinet 42U Freestanding rack Grey:

NetShelter SX Networking Enclosure expands Schneider Electric's superior IT enclosure line with improved support for high density networking applications. Integrated high density cable managers and improved cable access roof provide support for large cable bundles. When combined with the Side Airflow Duct Kit, the Networking Enclosure ensures complete isolation of cold intake and hot exhaust air for large switches and SAN directors.
APC AR3340G. Type: Freestanding rack, Rack capacity: 42U, Maximum weight capacity: 1704 kg. Weight: 161.4 kg. Product colour: Grey



Features	
Rack capacity *	42U
Type *	Freestanding rack
Maximum weight capacity *	1704 kg
Product colour	Grey
Certification	REACH, RoHS, UL 2416, UL 60950-1
Weight & dimensions	
Size (imperial)	48.3 cm (19")
Width	750 mm
Depth	1200 mm

Weight & dimensions	
Height	1991 mm
Weight	161.4 kg
Packaging data	
Package width	850 mm
Package depth	1320 mm
Package height	2118 mm
Package weight	183.2 kg
Logistics data	
Harmonized System (HS) code	85381000



0731304322498



731304322498

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 28-APR-2026. Prints or copies of Information are only valid on the printed Publication date