



DELL 1.8m, NEMA 5-15 - C13 IEC Black NEMA 5-15P C13 coupler

Brand : DELL

Product code: A8376158

Product name : 1.8m, NEMA 5-15 - C13 IEC

1.8m 18 AWG North American Power Cord (NEMA 5-15P to IEC320C13) (6ft)

DELL 1.8m, NEMA 5-15 - C13 IEC Black NEMA 5-15P C13 coupler:

Replace your overused or misplaced power cable, or just get some extra cords for convenience. This North American power cord is designed to work with most PCs, monitors, scanners, printers and other devices that use the 3-pin "Kettle Lead" shroud power connector. Plus this heavy duty 18 AWG cord features a fully moulded design for maximum durability and long life.

The female connector plugs directly into the device while the male connector plugs into a standard outlet.

Please note: This cable is suitable for use only with North American (USA or Canadian) power outlets.

- Replacement power cord for PC, monitor, printer, scanner, etc.
- Suitable for USA & Canada
- Perfect replacement for old, unreliable power cables
- Work with most PCs, monitors, scanners, and printers

DELL 1.8m, NEMA 5-15 - C13 IEC. Cable length: 1.8 m, Connector 1: NEMA 5-15P, Connector 2: C13 coupler. Input voltage: 125 V, Input current: 10 A



Features		Power	
Product colour *	Black	Input current	10 A
Connector 1 gender *	Male	Operational conditions	
Connector 2 gender *	Female	Storage temperature (T-T)	-20 - 60 °C
Cable length *	1.8 m	Certificates	
Connector 1 *	NEMA 5-15P	Compliance certificates	RoHS
Connector 2 *	C13 coupler	Certification	UL-E135710, CSA-LL95737
Power		Logistics data	
Input voltage	125 V	Harmonized System (HS) code	84733080



0757120806721



757120806721

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.