
Epson Matte Paper Heavy Weight - A4 - 50 Sheets



Brand : Epson

Product code: C13S041256

Product name : Matte Paper Heavy Weight - A4 - 50 Sheets

Matte Paper Heavy Weight - A4 - 50 Sheets

Epson Matte Paper Heavy Weight - A4 - 50 Sheets:

The light-white matt surface of this 167 g/m² printing medium ensures a more even colour distribution, resulting in this product being ideally suited for many applications both for beginners and for professional users. Photographers and graphic designers are thus in a position to produce high-quality photographs and pictures with a matt photo-like finish.
Epson Matte Paper Heavy Weight - A4 - 50 Sheets. Finish type: Matte, Media weight: 167 g/m², Paper size: A4. Width: 210 mm, Height: 297 mm. Quantity per pack: 1 pc(s), Package width: 220 mm, Package depth: 310 mm. Pallet width (UK): 100 cm, Pallet length (UK): 120 cm, Pallet height (UK): 105 cm.
Country of origin: Japan

Features	
Paper size	A4
Product colour	White
Finish type *	Matte
Media weight *	167 g/m²
Sheets per pack	50 sheets

Features	
Compatible products	WorkForce WF-7620DTWF WorkForce WF-7610DWF WorkForce WF-7110DTW WorkForce WF-3640DTWF WorkForce WF-3620DWF WorkForce WF-3520DWF WorkForce WF-2760DWF WorkForce WF-2750DWF WorkForce WF-2660DWF WorkForce WF-2650DWF WorkForce WF-2630WF WorkForce WF-2010W WorkForce WF-100W WorkForce Pro WF-C5790DWF WorkForce Pro WF-C5790DWF BAM WorkForce Pro WF-C5790DWF WorkForce Pro WF-4640DTWF WorkForce Pro WF-4630DWF SureColor SC-T7200D SureColor SC-T7200 SureColor SC-T5200PS SureColor SC-T5200D-PS SureColor SC-T5200D SureColor SC-T5200 SureColor SC-T5200 SureColor SC-T3405N SureColor SC-T3400N SureColor SC-T3400 SureColor SC-T3200N SureColor SC-T3200-PS SureColor SC-T3200 SureColor SC-T3100x 220V SureColor SC-T3100 SureColor SC-T300 SureColor SC-P9500 SureColor SC-P9000V SureColor SC-P9000 SureColor SC-P900 SureColor SC-P8000 SureColor SC-P800 SureColor SC-P7500 SureColor SC-P7000V SureColor SC-P7000 SureColor SC-P700 SureColor SC-P6000 SureColor SC-P600 SureColor SC-P5000 SureColor SC-P400 SureColor SC-P20000 SureColor SC-P10000 Expression Premium XP-900 Expression Premium XP-820 Expression Premium XP-810 Expression Premium XP-720 Expression Premium XP-7100 Expression Premium XP-645 Expression Premium XP-640 Expression Premium XP-635 Expression Premium XP-630 Expression Premium XP-625 Expression Premium XP-620 Expression Premium XP-615 Expression Premium XP-610 Expression Premium XP-540 Expression Premium XP-530 Expression Premium XP-520 Expression Premium XP-510 Expression Photo XP-970 Expression Photo XP-960 Expression Photo XP-950 Expression Photo XP-860 Expression Photo XP-850 Expression Photo XP-760 Expression Photo XP-750 Expression Photo XP-55 Expression Home XP-455 Expression Home XP-452 Expression Home XP-445 Expression Home XP-442 Expression Home XP-435 Expression Home XP-432 Expression Home XP-425 Expression Home XP-422 Expression Home XP-415 Expression Home XP-412 Expression Home XP-355 Expression Home XP-352 Expression Home XP-345 Expression Home XP-342 Expression Home XP-257 Expression Home XP-255 Expression Home XP-247 Expression Home XP-245 Expression Home XP-235 Expression Home XP-225 Expression Home XP-215 Epson WorkForce WF-7525 Epson WorkForce WF-7515 Epson WorkForce WF-7015 Epson WorkForce WF-3540DTWF Epson WorkForce WF-3010DW Epson SureColor SC-T7000 Epson SureColor SC-T5000 Epson SureColor SC-T3000 Epson Stylus SX620FW Epson Stylus SX610FW Epson Stylus SX600FW Epson Stylus SX525WD Epson Stylus SX515W Epson Stylus SX510W Epson Stylus SX445W Epson Stylus SX440W Epson Stylus SX435W Epson Stylus SX420W Epson Stylus SX415 Epson Stylus SX410 Epson Stylus SX405WiFi Epson Stylus SX405 Epson Stylus SX400 Epson Stylus SX235W Epson Stylus SX218 Epson Stylus SX215 Epson Stylus SX210 Epson Stylus SX205 Epson Stylus SX200 Epson Stylus SX130 Epson Stylus SX125 Epson Stylus SX115 Epson Stylus SX110 Epson Stylus SX105 Epson Stylus SX100 Epson Stylus S22 Epson Stylus S21 Epson Stylus S20 Epson Stylus Pro 9900 Epson Stylus Pro 9880 Epson Stylus Pro 9800 Epson Stylus Pro 9700 Epson Stylus Pro 9450 Epson Stylus Pro 9400 Epson Stylus Pro 7900 Epson Stylus Pro 7880 Epson Stylus Pro 7800 Epson Stylus Pro 7700 Epson Stylus Pro 7450 Epson Stylus Pro 7400 Epson Stylus Pro 5500 Epson Stylus Pro 4900 Epson Stylus Pro 4880 Epson Stylus Pro 4800 Epson Stylus Pro 4450 Epson Stylus Pro 4400 Epson Stylus Pro 3880 Epson Stylus Pro 3800 Epson Stylus Pro 11880 Epson Stylus Photo RX700 Epson Stylus Photo RX685 Epson Stylus Photo RX640 Epson Stylus Photo RX600 Epson Stylus Photo RX585 Epson Stylus Photo RX560 Epson Stylus Photo RX520 Epson Stylus Photo RX500 Epson Stylus Photo RX420 Epson Stylus Photo R800 Epson Stylus Photo R360 Epson Stylus Photo R3000 Epson Stylus Photo R300 Epson Stylus Photo R2880 Epson Stylus Photo R285 Epson Stylus Photo R265 Epson Stylus Photo R2400 Epson Stylus Photo R240 Epson Stylus Photo R2000 Epson Stylus Photo R200 Epson Stylus Photo R1900 Epson Stylus Photo R1800 Epson Stylus Photo PX830FWD Epson Stylus Photo PX820FWD Epson Stylus Photo PX810FW Epson Stylus Photo PX730WD Epson Stylus Photo PX720WD Epson Stylus Photo PX710W Epson Stylus Photo PX700W Epson Stylus Photo PX660 Epson Stylus Photo PX650 Epson Stylus Photo P50 Epson Stylus Photo 950 Epson Stylus Photo 935 Epson Stylus Photo 925 Epson Stylus Photo 915 Epson Stylus Photo 900 Epson Stylus Photo 895 Epson Stylus Photo 890 Epson Stylus Photo 870 Epson Stylus Photo 830U Epson Stylus Photo 830 Epson Stylus Photo 810 Epson Stylus Photo 1500W Epson Stylus Photo 1400 Epson Stylus Photo 1290S Epson Stylus Photo 1290 Epson Stylus Office BX935FWD Epson Stylus Office BX925FWD Epson Stylus Office BX635FWD Epson Stylus Office BX630FW Epson Stylus Office BX625FWD Epson Stylus Office BX610FW Epson Stylus Office BX600FW Epson Stylus Office BX525WD Epson Stylus Office BX320FW Epson Stylus Office BX310FN Epson Stylus Office BX305FW Plus Epson Stylus Office BX305FW Epson Stylus Office BX305F Epson Stylus Office BX300F Epson Stylus Office B42WD Epson Stylus Office B40W Epson Stylus Office B1100 Epson Stylus DX9400F Epson Stylus DX8450 Epson Stylus DX8400 Epson Stylus DX7450 Epson Stylus DX7400 Epson Stylus DX7000F Epson Stylus DX6000 Epson Stylus DX5000 Epson Stylus DX4850 Epson Stylus DX4800 Epson Stylus DX4450 Epson Stylus DX4400 Epson Stylus DX4250 Epson Stylus DX4200 Epson Stylus DX4000 Epson Stylus DX3850+ Epson Stylus DX3850 Epson Stylus DX3800 Epson Stylus D92 Epson Stylus D88+ Epson Stylus D88 Epson Stylus D78 Epson Stylus D68 Photo Edition Epson Stylus D120 Epson Stylus Color 680 Epson Stylus Color 1160 Epson Stylus CX6600 Epson Stylus CX6400 Epson Stylus CX5400 Epson Stylus CX5200 Epson Stylus CX3650 Epson Stylus CX3200 Epson Stylus C86 Epson Stylus C84WiFi Epson Stylus C84N Epson Stylus C84 Epson Stylus C82N Epson Stylus C82 Epson Stylus C66 Epson Stylus C64 Epson Stylus C62 Epson Stylus C60 Epson Stylus C48 Epson Stylus C46 Epson Stylus C44+ Epson Stylus C42UX Epson Stylus C42+ Epson Stylus C40UX Epson Stylus C20UX Epson Expression Premium XP-800 Epson Expression Premium XP-700 Epson Expression Premium XP-605 Epson Expression Premium XP-600 Epson Expression Home XP-405WH Epson Expression Home XP-405 Epson Expression Home XP-402 Epson Expression Home XP-305 Epson Expression Home XP-302 Epson Expression Home XP-205 Epson Expression Home XP-202 Epson Expression Home XP-102 Epson EC-01 EcoTank L555 EcoTank L355 EcoTank ET-7750 EcoTank ET-7700 EcoTank ET-4750 EcoTank ET-4500 EcoTank ET-3750 EcoTank ET-3700 EcoTank ET-2756 EcoTank ET-2751 EcoTank ET-2750 EcoTank ET-2700 EcoTank ET-2650 EcoTank ET-2600 EcoTank ET-16500 EcoTank ET-14000

Weight & dimensions

Width	210 mm
Height	297 mm

Packaging data

Quantity per pack	1 pc(s)
Package width	220 mm
Package depth	310 mm
Package height	15 mm
Package weight	650 g

Logistics data

Harmonized System (HS) code	37032000
Pallet width (UK)	100 cm
Pallet length (UK)	120 cm
Pallet height (UK)	105 cm
Pallet gross width	80 cm
Pallet gross length	120 cm
Pallet gross height	105 cm
Products per pallet	500 pc(s)
Products per pallet (UK)	700 pc(s)

Logistics data	
Products per pallet layer	100 pc(s)
Products per pallet layer (UK)	140 pc(s)
Master (outer) case width	330 mm
Master (outer) case length	470 mm
Master (outer) case height	210 mm
Master (outer) case gross weight	14 g
Products per master (outer) case	20 pc(s)
Minimum order quantity	20 pc(s)

Other features	
Country of origin	Japan

0010343818439

010343818439

Catalog Object Cloud

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 28-APR-2026. Prints or copies of Information are only valid on the printed Publication date