



Lenovo 1754D2X KVM switch Rack mounting Black

Brand : Lenovo

Product name : 1754D2X

Product code: 1754D2X



Global Console Manager GCM32, 32 ports, Rack 1U, Black

Lenovo 1754D2X KVM switch Rack mounting Black:

The IBM GCM32 Global Console Manager includes the following items:

- 32-port console switch
- Mounting hardware for EIA space for rack sidewall compartment
- One 1U filler panel
- Two C13/C14 rack power cables
- RJ45-DB9F DCE adapter for use with Setup port
- RJ45-DB9M DTE adapter for use with Modem port
- 32 terminators for daisy-chaining configurations
- Installation publications and warranty

Lenovo 1754D2X. Keyboard port type: USB, Mouse port type: USB, Video port type: VGA. Cabling technology: 10/100/1000Base-T(X), Networking standards: IEEE 802.3, IEEE 802.3ab, IEEE 802.3u. Maximum resolution: 1600 x 1200 pixels. Product colour: Black, Rack capacity: 1U. Input voltage: 100-240 V, AC input frequency: 50 - 60 Hz, Power consumption (typical): 24 W

Ports & interfaces		Display	
Keyboard port type *	USB	Built-in display *	✗
Mouse port type *	USB		
Video port type *	VGA		
VGA (D-Sub) ports quantity	1		
USB 2.0 ports quantity	4		
Audio connections	✗		
Console port	RJ-45		
Network		Power	
Ethernet LAN	✓	Input voltage	100-240 V
Ethernet LAN (RJ-45) ports	32	AC input frequency	50 - 60 Hz
Cabling technology	10/100/1000Base-T(X)	Power consumption (typical)	24 W
Networking standards	IEEE 802.3, IEEE 802.3ab, IEEE 802.3u		
Performance		Operational conditions	
Maximum resolution *	1600 x 1200 pixels	Operating temperature (T-T)	0 - 50 °C
		Storage temperature (T-T)	-20 - 70 °C
		Operating relative humidity (H-H)	20 - 80%
		Storage relative humidity (H-H)	5 - 95%
Design		Weight & dimensions	
Rack mounting *	✓	Width	431.8 mm
Rack capacity	1U	Depth	324 mm
Product colour *	Black	Height	43.7 mm
		Weight	3.5 kg
		Logistics data	
		Harmonized System (HS) code	85176200



0883436082877



883436082877

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.