# Epson Standard Capacity Toner Cartridge Yellow 1.5k



**Brand :** Epson

**Product code:** C13S050191

**Product name :** Standard Capacity Toner Cartridge Yellow 1.5k

Standard Capacity Toner Cartridge Yellow 1.5k

Epson Standard Capacity Toner Cartridge Yellow 1.5k:

Epson AcuBrite toner for the highest printing quality. The Epson AcuBrite Toner ensures brilliant colours and excellent colour stability.
Epson Standard Capacity Toner Cartridge Yellow 1.5k. Colour toner page yield: 1500 pages, Printing colours: Yellow, Quantity per pack: 1 pc(s)

| Features | |
|---|---|
| Compatibility * | C1100N, CX11NFC, CX11N, CX11NFCT, CX11NF, CX11NFT |
| Quantity per pack * | 1 pc(s) |
| Colour toner page yield * | 1500 pages |
| Type * | Original |
| Printing colours * | Yellow |
| Brand compatibility * | Epson |
| Cartridge capacity | Standard Yield |
| Country of origin | Japan |
| **Weight & dimensions** | |
| Weight | 330 g |
| Dimensions (WxDxH) | 336 x 85 x 85 mm |
| **Packaging data** | |
| Package width | 80 mm |
| Package depth | 330 mm |
| Package height | 80 mm |
| Package weight | 0.39 g |
| **Other features** | |
| Colour | ✔ |

| Other features | |
|---|---|
| Print technology | Laser printing |
| **Logistics data** | |
| Harmonized System (HS) code | 84439990 |
| Products per master (outer) case | 20 pc(s) |
| Master (outer) case width | 360 mm |
| Master (outer) case length | 380 mm |
| Master (outer) case height | 475 mm |
| Products per pallet layer | 120 pc(s) |
| Products per pallet layer (UK) | 120 pc(s) |
| Products per pallet | 480 pc(s) |
| Products per pallet (UK) | 480 pc(s) |
| Pallet gross width | 80 cm |
| Pallet gross length | 120 cm |
| Pallet gross height | 95 cm |
| Pallet width (UK) | 100 cm |
| Pallet length (UK) | 120 cm |
| Pallet height (UK) | 95 cm |

0010343605886

010343605886

**Catalog Object Cloud**

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 28-APR-2026. Prints or copies of Information are only valid on the printed Publication date