



HP Q6998A output stacker 1600 sheets

Brand : HP
Product name : Q6998A
Product code: Q6998A

1600 sheet, 54 kg, White, Black

HP Q6998A output stacker 1600 sheets:

Get a maximum output capacity in three bins and retrieve jobs less frequently with this output accessory.


- Save time - streamline workflow processes with automatic job stapling. Staple up to 50 pages per document with a single corner staple or multiple side staples.
 - The intelligent function-separator capability of this output accessory enables efficient department workflows. Walk-up copy, print, and fax jobs are sent to different output trays for ease of collection. All bins also support offset sorting.
 - Increase output capacity, sort jobs, and eliminate time-consuming manual processes with this accessory. Staple up to 50 pages per document.
- HP Q6998A. Maximum capacity: 1600 sheets, Stapling capacity: 50 sheets. Width: 635 mm, Depth: 616 mm, Height: 1104.9 mm



Features		Weight & dimensions	
Maximum capacity	1600 sheets	Width	635 mm
Stapler	✓	Depth	616 mm
Stapling capacity	50 sheets	Height	1104.9 mm
		Weight	54 kg



0882780555266



882780555266

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.