# Canon PGI-9CO Clear Ink Cartridge (Chroma Optimiser)

**Brand :** Canon

**Product code:** 2442B001

**Product name :** PGI-9CO Clear Ink Cartridge (Chroma Optimiser)

- Genuine Canon Ink produces on average 35% more quality prints than imitation cartridges†††
- Genuine Canon Ink provides consistent quality prints 100% of the time†††
- Genuine Canon Ink is 100% reliable so you can print with less stress†††
- Return every ink and toner cartridge to be reused or recycled. It's free, easy and environmentally friendly.

PGI-9CO Clear Ink Cartridge (Chroma Optimiser)

Canon PGI-9CO Clear Ink Cartridge (Chroma Optimiser):

Part of the PgR technology where surface of plain paper is coated with a layer of clear ink before colour printing. It delivers laser-quality plain paper prints ideal for leaflets and posters. The 191ml clear ink tank allows you to print up to 1625 pages of A4 documents at ISO/IEC 24711† standard.
Canon PGI-9CO Clear Ink Cartridge (Chroma Optimiser). Colour ink page yield: 1625 pages, Quantity per pack: 1 pc(s)

| Features | |
|---|---|
| Print technology | Inkjet printing |
| Compatibility * | PIXMA iX7000/MX7600 |
| Quantity per pack * | 1 pc(s) |
| Colour ink page yield * | 1625 pages |
| Type * | Original |

| Packaging data | |
|---|---|
| Package width | 110 mm |
| Package depth | 70 mm |
| Package height | 50 mm |
| Package weight | 300 g |

| Logistics data | |
|---|---|
| Harmonized System (HS) code | 84439990 |

4960999534619

**Catalog Object Cloud**

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 28-APR-2026. Prints or copies of Information are only valid on the printed Publication date