



APC Basic Rack PDU power distribution unit (PDU) 24 AC outlet(s)
0U Black

Brand : APC

Product code: AP7551

Product name : Basic Rack PDU

Rack PDU,Basic,ZeroU,16A,230V,(20)C13 & (4)C19; IEC309

APC Basic Rack PDU power distribution unit (PDU) 24 AC outlet(s) 0U Black:

APC Basic Rack PDU, Input: 230V, Input Connections: IEC 309 16A 2P+E, Cord Length: 3 feet (0.91 meters), Output: 230V, Output Connections: IEC 320 C13, IEC 320 C19.

Includes: Installation guide, Toolless Mounting Kit.

APC Basic Rack PDU. PDU types: Basic, Rack capacity: 0U, Mounting: Vertical. AC outlets quantity: 24 AC outlet(s), AC outlet types: C13 coupler, C19 coupler, Input connection type: IEC 309 16A 2P+E. Cable length: 0.91 m. Nominal input voltage: 230 V, Nominal output voltage: 230 V, Load capacity: 3680 VA. Certification: CCC,CE,GOST,IRAM,VDE

Design		Certificates	
PDU types *	Basic	Certification	CCC,CE,GOST,IRAM,VDE
Rack capacity *	0U	Operational conditions	
Mounting	Vertical	Operating temperature (T-T)	0 - 45 °C
Product colour	Black	Storage temperature (T-T)	-25 - 65 °C
Ports & interfaces		Operating relative humidity (H-H)	5 - 95%
AC outlets quantity *	24 AC outlet(s)	Storage relative humidity (H-H)	5 - 95%
AC outlet types *	C13 coupler, C19 coupler	Weight & dimensions	
I/O ports	IEC-309 16 A plug (20) IEC-320-C13 (4) IEC-320-C19	Width	55.9 mm
Input connection type	IEC 309 16A 2P+E	Depth	43.9 mm
Features		Height	1619.3 mm
Cable length	0.91 m	Weight	4.86 kg
Power		Packaging data	
Nominal input voltage *	230 V	Package weight	5.77 kg
Nominal output voltage	230 V	Package width	152 mm
Load capacity	3680 VA	Package depth	127 mm
Maximum input current per phase	16 A	Package height	2134 mm
Maximum power	3680 W		





0731304207917



731304207917

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.