# Canon CL-513 C/M/Y Colour Ink Cartridge

**Brand :** Canon

**Product code:** 2971B001

**Product name :** CL-513 C/M/Y Colour Ink Cartridge

- Genuine Canon Ink produces on average 35% more quality prints than imitation cartridges†††
- Genuine Canon Ink provides consistent quality prints 100% of the time†††
- Genuine Canon Ink is 100% reliable so you can print with less stress†††
- Return every toner ink and toner cartridge to be reused or recycled. It's free, easy and environmentally friendly.

CL-513 C/M/Y Colour Ink Cartridge

Canon CL-513 C/M/Y Colour Ink Cartridge:

This high yield colour ink provides more prints than the standard equivalent. The tri-colour ink tank with ChromaLife100+ system is used for printing colour documents and photos. This 13ml colour ink cartridge allows you to print up to 349 pages of A4 document at ISO/IEC 24711† standard.
Canon CL-513 C/M/Y Colour Ink Cartridge. Colour ink type: Pigment-based ink, Colour ink page yield: 349 pages, Printing colours: Cyan, Magenta, Yellow, Quantity per pack: 1 pc(s)

| Features | |
|---|---|
| Colour ink type | Pigment-based ink |
| Print technology | Inkjet printing |
| Compatibility * | MP240/MP260/MP480/MX300/MX310 |
| Quantity per pack * | 1 pc(s) |
| Colour ink page yield * | 349 pages |
| Type * | Original |
| Ink type | Pigment-based ink |
| Printing colours * | Cyan, Magenta, Yellow |

| Features | |
|---|---|
| Country of origin | Japan |
| Colour | ✔ |
| **Packaging data** | |
| Package width | 145 mm |
| Package depth | 85 mm |
| Package height | 55 mm |
| Package weight | 70 g |
| **Logistics data** | |
| Harmonized System (HS) code | 84439990 |

4960999617022

**Catalog Object Cloud**

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 28-APR-2026. Prints or copies of Information are only valid on the printed Publication date