

StarTech.com 80x25mm Ball Bearing Quiet Computer Case Fan w/ TX3 Connector

Brand : StarTech.com

Product code: FAN8X25TX3L

Product name : 80x25mm Ball Bearing Quiet Computer Case Fan w/ TX3 Connector



StarTech.com 80x25mm Ball Bearing Quiet Computer Case Fan w/ TX3 Connector - 3 pin case Fan - TX3 Fan - computer case Fan

[StarTech.com 80x25mm Ball Bearing Quiet Computer Case Fan w/ TX3 Connector:](#)

Add additional chassis cooling with a 80mm ball bearing fan

This quiet, dual ball-bearing (8cm) Case Fan offers a cost-effective solution for replacing a non-functional or noisy fan in your PC.

Powered through a simple TX3 connection to the host computer's motherboard, the 8cm case fan helps keep your computer running at optimal temperatures for stable system performance.

The StarTech.com Advantage

- A dual ball bearing design ensures reliability and longer life
- A built-in tachometer allows for easy monitoring of the fan performance
- Backed by a StarTech.com 2-year warranty and free lifetime technical support

Performance		Weight & dimensions	
Suitable location *	Computer case	Depth	80 mm
Type *	Fan	Height	80 mm
Fan diameter	8 cm	Weight	73 g
Rotational speed (max)	2000 RPM	Package width	97 mm
Noise level (high speed)	27 dB	Package depth	143 mm
Maximum airflow	26.6 cfm	Package height	32 mm
Operating temperature (T-T)	-10 - 80 °C	Package weight	98 g
Design		Technical details	
Product colour *	Black	Compliance certificates	RoHS
Material	Plastic	Other features	
Number of fans	1 fan(s)	Dimensions (WxDxH)	80 x 80 x 25 mm
Power		Power requirements	12 V
Voltage	12 V	Airflow	26.6
Weight & dimensions		Rotational speed	2000 RPM
Width	25 mm	Logistics data	
		Harmonized System (HS) code	84733080



0065030788885



065030788885



0650307888858



650307888858

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.