



Lenovo 4X20M26256 mobile device charger Laptop, Tablet Black
AC Indoor

Brand : Lenovo

Product code: 4X20M26256

Product name : 4X20M26256



Lenovo 45W Standard AC Adapter (USB Type-C)

Lenovo 4X20M26256 mobile device charger Laptop, Tablet Black AC Indoor:

This Lenovo 45W Standard AC Adapter (USB Type-C) Power Adapter offers fast, efficient charging at home, in the office, or on the go. This power adapter is compatible with ThinkPad USB-C enabled Notebook and Tablet.Smart Voltage: Its PD technology automatically detects and delivers 5V/2A,9V/2A ,15V/3A or 20V/2.25A

Tested and reliable: tested, reliable and backed by a one-year limited warranty

Lenovo 4X20M26256. Charger type: Indoor, Power source type: AC, Charger compatibility: Laptop, Tablet. Input voltage: 100 - 240 V. USB Type-C ports quantity: 1. Product colour: Black

Performance		Weight & dimensions	
Charger compatibility *	Laptop, Tablet	Depth	93 mm
Power source type *	AC	Height	28.5 mm
Micro-USB 3.2 Gen 1 (3.1 Gen 1) ports quantity	1	Weight	170 g
USB Type-C ports quantity	1	Operational conditions	
Charger type *	Indoor	Operating temperature (T-T)	5 - 40 °C
Operating principle	Contact	Operating relative humidity (H-H)	8 - 80%
Design		Packaging content	
Product colour *	Black	Included power plug types	EU
Power		Certificates	
Input voltage	100 - 240 V	Certification	IARM (Argentina), ICES, CECP, C-Tick, C-UL, FCC, KC, NEMKO, PSE, PSB, BSMI, CE, GOST, GS
Input frequency	50/60 Hz		
Power supply	45 W		
Weight & dimensions		Logistics data	
Width	40 mm	Harmonized System (HS) code	85044095
Other features			
		Integrated USB cable	✓



0191200521720



191200521720

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.