

StarTech.com 3 ft Panel Mount USB Cable - USB A to Motherboard Header Cable F/F

Brand : StarTech.com

Product code: USBPNLAFHD3

Product name : 3 ft Panel Mount USB Cable - USB A to Motherboard Header Cable F/F

StarTech.com 3 ft Panel Mount USB Cable - USB A to Motherboard Header Cable F/F - USB A-Female to USB Header Adapter - USB-A (F) Port, 3ft

StarTech.com 3 ft Panel Mount USB Cable - USB A to Motherboard Header Cable F/F:

Connect a panel mount USB-A port to your motherboard header

The USBPNLAFHD3 3ft Panel Mount USB Cable enables you to add a well-secured, easy to access USB 2.0 port to your PC, offering a convenient solution for connecting bootable thumb drives or authentication fobs etc. to the motherboard USB connection.

The adapter features one female USB header connector and one female panel mount USB-A port and gives you an extension of 3ft, enabling you to place the cable as needed within the system case.

The USBPNLAFHD3 is backed by StarTech.com's lifetime warranty for guaranteed reliability.

The StarTech.com Advantage

StarTech.com 3 ft Panel Mount USB Cable - USB A to Motherboard Header Cable F/F. Cable length: 0.9 m. Connector contacts plating: Nickel, Product colour: Black



Features		Packaging data	
Connector 1 gender *	Female	Package width	125 mm
Connector 2 gender *	Female	Package depth	225 mm
AWG wire size	24/28	Package height	16 mm
Connector contacts plating	Nickel	Package weight	40 g
Cable shielding	Aluminum mylar foil	Operational conditions	
Product colour *	Black	Operating temperature (T-T)	0 - 40 °C
Weight & dimensions		Certificates	
Cable length *	0.9 m	Compliance certificates	RoHS
Width	38 mm	Certification	CE, UL, REACH
Depth	900 mm	Logistics data	
Height	10 mm	Harmonized System (HS) code	84733080
Weight	34 g		



0065030852081



065030852081



0723856363005



723856363005

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.