Epson Seahorse Singlepack Black T0481



Brand : Epson **Product family:** Seahorse **Product code:** C13T04814010

Product name : Singlepack Black T0481

Singlepack Black T0481

Epson Seahorse Singlepack Black T0481:

Epson Original ink cartridges are optimally suited to your printer. These highly reliable cartridges guarantee long printout life and trouble-free printing for many years to come.
Epson Seahorse Singlepack Black T0481. Black ink type: Pigment-based ink, Printing colours: Black, Quantity per pack: 1 pc(s)

Features	
Black ink type	Pigment-based ink
Compatibility *	Epson Stylus Photo R200, R220, R300, R320, R340, RX500, RX600, RX620, RX640
Quantity per pack *	1 pc(s)
Type *	Original
Ink type	Pigment-based ink
Printing colours *	Black
Brand compatibility *	Epson
Country of origin	Mexico
Operational conditions	
Storage temperature (T-T)	-20 - 40 °C
Weight & dimensions	
Width	246 mm
Depth	116 mm
Height	145 mm
Weight	59 g
Packaging data	
Package width	145 mm
Package depth	33 mm

Packaging data	
Package height	120 mm
Package weight	100 g
Other features	
Certification	CE
Logistics data	
Pallet gross width	80 cm
Pallet gross length	120 cm
Pallet gross height	161 cm
Products per pallet	2400 pc(s)
Master (outer) case width	120 mm
Master (outer) case length	260 mm
Master (outer) case height	146 mm
Products per master (outer) case	8 pc(s)
Harmonized System (HS) code	84439990
Products per pallet (UK)	2400 pc(s)
Products per pallet layer	240 pc(s)
Products per pallet layer (UK)	240 pc(s)
Minimum order quantity	8 pc(s)

8715946356020

Catalog Object Cloud

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 28-APR-2026. Prints or copies of Information are only valid on the printed Publication date