

Epson Singlepack Photo Black T614100 220 ml

Brand : Epson

Product code: C13T614100



Product name : Singlepack Photo Black T614100 220 ml

Singlepack Photo Black T614100 220 ml

Epson Singlepack Photo Black T614100 220 ml:

The objective in developing the UltraChrome pigment ink was to combine the long-term and short-term colour stability properties of pigment inks with the colour scale of dye inks. This new colour ink system includes light black as a seventh colour, which makes it possible to achieve softer gradations in the case of black&white printing, as well as two types of black ink, matt & photo, ensuring that optimal quality can be achieved on all media types.

Epson Singlepack Photo Black T614100 220 ml. Colour ink type: Dye-based ink, Black ink volume: 220 ml, Printing colours: Photo black, Quantity per pack: 1 pc(s)

Features		Packaging data	
Colour ink type	Dye-based ink	Package depth	290 mm
Print technology	Inkjet printing	Package height	110 mm
Compatibility *	STYLUS PRO 4400	Package weight	0.44 g
Quantity per pack *	1 pc(s)	Logistics data	
Black ink cartridges quantity	1	Pallet gross width	80 cm
Black ink volume	220 ml	Pallet gross length	120 cm
Type *	Original	Pallet gross height	4.2 m
Ink type	Dye-based ink	Products per pallet	1200 pc(s)
Printing colours *	Photo black	Harmonized System (HS) code	84439990
Brand compatibility *	Epson	Pallet width (UK)	100 cm
OEM code	C13T614100	Pallet length (UK)	120 cm
Country of origin	China	Pallet height (UK)	4.2 m
Packaging data		Products per pallet (UK)	1680 pc(s)
Package width	30 mm	Products per pallet layer	120 pc(s)
		Products per pallet layer (UK)	168 pc(s)



0010343866027



010343866027

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.